




Single and Dual In-Line Resistor Networks



The model 4600 is a conformal coated and the model 4300 is a molded single in-line package resistor networks. Their low profile is compatible with DIPs. They are recommended for rosin flux and solvent clean or no clean flux processes. The 4100 series is a molded dual in-line network. Gold Epoxy provides excellent marking contrast for permanent laser marking on all three series. All are compatible with automatic insertion equipment. All are also available in additional values, dual terminators, additional pin count and additional profiles. Call for quote. Manufacturer's literature available upon request.

11

Stock No.	Mfr.'s Type	Ohms	Circuit	Pin Count	Watts	EACH			
						1-9	10-24	25-49	50-99
755-4721	4114R-1-102	1K	Isolated	14	2.00	.45	.43	.42	.40
755-4734	4114R-1-103	10K	Isolated	14	2.00	.48	.44	.40	.38
755-4711	4114R-1-15	150	Isolated	14	2.00	.48	.44	.40	.38
755-4713	4114R-1-22	220	Isolated	14	2.00	.45	.41	.38	.36
755-4715	4114R-1-331	330	Isolated	14	2.00	.49	.44	.41	.39
755-4934	4114R-2-103	10K	Bussed	14	2.00	.48	.44	.40	.38
755-4930	4114R-2-472	4.7K	Bussed	14	2.00	.48	.44	.40	.39
755-4809	4116R-1-101	100	Isolated	16	2.25	.48	.44	.40	.39
755-4821	4116R-1-102	1K	Isolated	16	2.25	.45	.41	.38	.37
755-4834	4116R-1-103	10K	Isolated	16	2.25	.45	.41	.38	.37
755-4847	4116R-1-104	100K	Isolated	16	2.25	.45	.41	.38	.37
755-4811	4116R-1-151	150	Isolated	16	2.25	.46	.41	.38	.37
755-4838	4116R-1-203	20K	Isolated	16	2.25	.48	.44	.40	.39
755-4813	4116R-1-221	220	Isolated	16	2.25	.45	.41	.38	.37
755-4826	4116R-1-222	2.2K	Isolated	16	2.25	.48	.44	.40	.39
755-4814	4116R-1-271	270	Isolated	16	2.25	.49	.45	.41	.40
755-4803	4116R-1-330	33	Isolated	16	2.25	.45	.41	.38	.37
755-4815	4116R-1-331	330	Isolated	16	2.25	.46	.41	.38	.37
755-4828	4116R-1-332	3.3K	Isolated	16	2.25	.45	.41	.38	.37
755-4816	4116R-1-391	390	Isolated	16	2.25	.45	.41	.38	.37
755-4817	4116R-1-471	470	Isolated	16	2.25	.48	.44	.40	.39
755-4830	4116R-1-472	4.7K	Isolated	16	2.25	.48	.44	.40	.39
755-4819	4116R-1-681	680	Isolated	16	2.25	.48	.44	.40	.39
755-5021	4116R-2-102	1K	Bussed	16	2.25	.48	.44	.41	.39
755-5034	4116R-2-103	10K	Bussed	16	2.25	.45	.41	.38	.36
755-5026	4116R-2-222	2.2K	Bussed	16	2.25	.45	.41	.38	.36
755-5030	4116R-2-472	4.7K	Bussed	16	2.25	.45	.41	.38	.36
755-6021	4306R-101-102	1K	Bussed	6	0.75	.41	.37	.35	.33
755-6034	4306R-101-103	10K	Bussed	6	0.75	.39	.37	.35	.34
755-6030	4306R-101-472	4.7K	Bussed	6	0.75	.39	.37	.36	.35
755-6121	4308R-101-102	1K	Bussed	8	1.00	.41	.38	.37	.36
755-6134	4308R-101-103	10K	Bussed	8	1.00	.39	.35	.33	.31
755-6126	4308R-101-222	2.2K	Bussed	8	1.00	.42	.40	.39	.38
755-6117	4308R-101-471	470	Bussed	8	1.00	.42	.37	.35	.33
755-6130	4308R-101-472	4.7K	—	8	1.00	.39	.35	.33	.31
755-6421	4308R-102-102	1K	Isolated	8	1.00	.43	.39	.36	.34
755-6434	4308R-102-103	10K	Isolated	8	1.00	.46	.41	.38	.36
755-6447	4308R-102-104	100K	Isolated	8	1.00	.43	.39	.36	.34
755-6428	4308R-102-332	3.3K	Isolated	8	1.00	.43	.39	.36	.34
755-6625	4308R-104-221/331	220/330	Dual	8	1.00	.70	.65	.60	.57
755-6221	4310R-101-102	1K	Bussed	10	1.25	.49	.44	.41	.39
755-6234	4310R-101-103	10K	Bussed	10	1.25	.52	.47	.44	.41
755-6247	4310R-101-104	100K	Bussed	10	1.25	.49	.44	.41	.39

Stock No.	Mfr.'s Type	Ohms	Circuit	Pin Count	Watts	EACH			
						1-9	10-24	25-49	50-99
755-6224	4310R-101-182	1.8K	Bussed	10	1.25	.49	.44	.41	.39
755-6213	4310R-101-221	220	Bussed	10	1.25	.52	.47	.44	.41
755-6226	4310R-101-222	2.2K	Bussed	10	1.25	.49	.44	.41	.39
755-6215	4310R-101-331	330	Bussed	10	1.25	.52	.47	.44	.41
755-6228	4310R-101-332	3.3K	Bussed	10	1.25	.52	.47	.44	.41
755-6230	4310R-101-472	4.7K	Bussed	10	1.25	.49	.44	.41	.39
755-6243	4310R-101-473	47K	Bussed	10	1.25	.52	.47	.44	.41
755-6534	4310R-102-103	10K	Bussed	10	1.25	.49	.44	.41	.39
755-6640	4310R-104-221/331	220/330	Dual	10	1.25	.82	.65	.59	.54
755-4021	4606X-101-102	1K	Bussed	6	0.75	.33	.26	.24	.22
755-4034	4606X-101-103	10K	Bussed	6	0.75	.33	.26	.24	.22
755-4047	4606X-101-104	100K	Bussed	6	0.75	.26	.21	.20	.19
755-4026	4606X-101-222	2.2K	Bussed	6	0.75	.33	.26	.24	.22
755-4039	4606X-101-223	22K	Bussed	6	0.75	.33	.26	.24	.22
755-4015	4606X-101-331	330	Bussed	6	0.75	.33	.26	.24	.22
755-4017	4606X-101-471	470	Bussed	6	0.75	.33	.26	.24	.22
755-4030	4606X-101-472	4.7K	Bussed	6	0.75	.33	.26	.24	.22
755-4043	4606X-101-473	47K	Bussed	6	0.75	.33	.26	.24	.22
755-4321	4606X-102-102	1K	Isolated	6	0.75	.33	.26	.24	.22
755-4334	4606X-102-103	10K	Isolated	6	0.75	.33	.26	.24	.22
755-4313	4606X-102-221	220	Isolated	6	0.75	.33	.26	.24	.22
755-4121	4608X-101-102	1K	Bussed	8	1.00	.35	.28	.26	.24
755-4134	4608X-101-103	10K	Bussed	8	1.00	.35	.28	.26	.24
755-4147	4608X-101-104	100K	Bussed	8	1.00	.35	.28	.26	.24
755-4113	4608X-101-221	220	Bussed	8	1.00	.35	.28	.26	.24
755-4126	4608X-101-222	2.2K	Bussed	8	1.00	.35	.28	.26	.24
755-4139	4608X-101-223	22K	Bussed	8	1.00	.35	.28	.26	.24
755-4115	4608X-101-331	330	Bussed	8	1.00	.29	.24	.22	.21
755-4128	4608X-101-332	3.3K	Bussed	8	1.00	.35	.28	.26	.24
755-4130	4608X-101-472	4.7K	Bussed	8	1.00	.29	.24	.22	.21
755-4143	4608X-101-473	47K	Bussed	8	1.00	.35	.28	.26	.24
755-4409	4608X-102-101	100	Isolated	8	1.00	.35	.28	.26	.24
755-4421	4608X-102-102	1K	Isolated	8	1.00	.35	.28	.26	.24
755-4434	4608X-102-103	10K	Isolated	8	1.00	.35	.28	.26	.24
755-4447	4608X-102-104	100K	Isolated	8	1.00	.35	.28	.26	.24
755-4459	4608X-102-105	1M	Isolated	8	1.00	.35	.28	.26	.24
755-4410	4608X-102-121	120	Isolated	8	1.00	.35	.28	.26	.24
755-4425	4608X-102-202	2K	Isolated	8	1.00	.35	.28	.26	.24
755-4426	4608X-102-222	2.2K	Isolated	8	1.00	.35	.28	.26	.24
755-4439	4608X-102-223	22K	Isolated	8	1.00	.35	.28	.26	.24
755-4414	4608X-102-271	270	Isolated	8	1.00	.35	.28	.26	.24
755-4403	4608X-102-330	33	Isolated	8	1.00	.35	.28	.26	.24
755-4415	4608X-102-331	330	Isolated	8	1.00	.35	.28	.26	.24
755-4405	4608X-102-470	47	Isolated	8	1.00	.35	.28	.26	.24
755-4417	4608X-102-471	470	Isolated	8	1.00	.35	.28	.26	.24
755-4430	4608X-102-472	4.7K	Isolated	8	1.00	.35	.28	.26	.24
755-4443	4608X-102-473	47K	Isolated	8	1.00	.35	.28	.26	.24
755-4209	4610X-101-101	100	Bussed	10	1.25	.37	.30	.28	.27
755-4221	4610X-101-102	1K	Bussed	10	1.25	.37	.30	.28	.27
755-4234	4610X-101-103	10K	Bussed	10	1.25	.43	.34	.32	.31
755-4247	4610X-101-104	100K	Bussed	10	1.25	.37	.30	.28	.27
755-4236	4610X-101-203	20K	Bussed	10	1.25	.37	.30	.28	.27
755-4213	4610X-101-221	220	Bussed	10	1.25	.37	.30	.28	.27
755-4226	4610X-101-222	2.2K	Bussed	10	1.25	.37	.30	.28	.27
755-4239	4610X-101-223	22K	Bussed	10	1.25	.37	.30	.28	.27
755-4227	4610X-101-272	2.7K	Bussed	10	1.25	.37	.30	.28	.27
755-4215	4610X-101-331	330	Bussed	10	1.25	.37	.30	.28	.27
755-4228	4610X-101-332	3.3K	Bussed	10	1.25	.37	.30	.28	.27
755-4217	4610X-101-471	470	Bussed	10	1.25	.37	.30	.28	.27
755-4230	4610X-101-472	4.7K	Bussed	10	1.25	.37	.30	.28	.27
755-4243	4610X-101-473	47K	Bussed	10	1.25	.37	.30	.28	.27
755-4255	4610X-101-474	470K	Bussed	10	1.25	.37	.30	.28	.27
755-4219	4610X-101-681	680	Bussed	10	1.25	.37	.30	.28	.27
755-4245	4610X-101-683	68K	Bussed	10	1.25	.37	.30	.28	.27
755-4521	4610X-102-102	1K	Isolated	10	1.25	.37	.30	.28	.27
755-4534	4610X-102-103	10K	Isolated	10	1.25	.37	.30	.28	.27
755-4547	4610X-102-104	100K	Isolated	10	1.25	.37	.30	.28	.27
755-4503	4610X-102-330	33	Isolated	10	1.25	.37	.30	.28	.27
755-4530	4610X-102-472	4.7K	Isolated	10	1.25	.37	.30	.28	.27