



## 10-32 Tapped Combination Mounting Rail *CCR Series*

Use with C2, C3 and REFK Series

### Features



- Constructed in 10-gauge steel
- Sold in pairs
- EIA-310-D compliant drilled and tapped 10-32 holes
- Rails come stamped and numbered in 1U (1.75") increments.
- Bolts vertically in cabinets.
- Use with **C2**, **C3** or **REFK** cabinets.
- Mounting hardware included:
  - Strut mounting hardware (for both rails).
- Rails are compatible for 19", 23" and 24" rack mounting.
- Side of rail flanged for rear support or accessory mounting (not compatible with server slides).
- Finished in Zinc steel plate.

Part No.	Mounting Dimensions	
	Rack Units	Height
<b>CCR22TZPL</b>	13U	22.75
<b>CCR35TZPL</b>	20U	35.00
<b>CCR42TZPL</b>	24U	42.00
<b>CCR49TZPL</b>	28U	49.00
<b>CCR56TZPL</b>	32U	56.00
<b>CCR63TZPL</b>	36U	63.00
<b>CCR70TZPL</b>	40U	70.00
<b>CCR77TZPL</b>	44U	77.00
<b>CCR78TZPL</b>	45U	78.75
<b>CCR85TZPL</b>	49U	85.75

*Data subject to change without notice*