

16 Dismantling Tools

16 20 16 SB



16 20 165 SB



- ▶ for stripping all common round cables
- ▶ self-cocking holding lever
- ▶ with adjusting screw for cutting depth adaptation
- ▶ turnable blade for circular and longitudinal cutting
- ▶ spare blade inside the handle
- ▶ impact resistant plastic body made of wear-resistant polyamide
- ▶ secure grip due to soft component material on handle and holding lever to avoid slipping

Model 16 20 16 SB:

- ▶ for cables from 4.0 up to 16.0 mm dia.

Model 16 20 165 SB

- ▶ with knife and hook blade inclusive protective cap
- ▶ for cables from 8.0 up to 28.0 mm dia.

Model 16 20 28 SB:

- ▶ for cables from 8.0 up to 28.0 mm dia.

Article-No.	EAN-Code	Handles	Stripping capacities		
			Length mm	mm	g
16 20 16 SB	060451	shock-resistant plastic body	4.0 - 16.0	5/16 - 1 1/8	80
16 20 165 SB	043133	shock-resistant plastic body	8.0 - 28.0	5/16 - 1 1/8	100
16 20 28 SB	060468	shock-resistant plastic body	8.0 - 28.0	5/16 - 1 1/8	80
16 29 165	043140	spare blade			



Self-turning drag blade for comfortable dismantling

16 Dismantling Tool

16 30 135 SB



- ▶ for dismantling round PVC, rubber, silicone, PTFE cables from 6.0 - 29.0 mm dia.
- ▶ self-cocking holding lever
- ▶ with knurled nut for cutting depth adjustment
- ▶ changing from circular to longitudinal cutting by turning the tool body
- ▶ spiral cutting for longer stripping areas
- ▶ shock-resistant plastic body
- ▶ exchangeable blade



Adjustable cutting depth for precise dismantling

Article-No.	EAN-Code	Handles	Stripping capacities		
			Length mm	mm	g
16 30 135 SB	026907	shock-resistant plastic body	6.0 - 29.0	15/64 - 1 9/64	115
16 39 135	027317	spare blade			