


Pin Haeder with Polarizing Feature and Friction Lock 2,54 mm

Series

428



Rated current	3,0 A
Rated voltage	250 VRMS / VDC
Please consider air- and creepage distances	
Withstand voltage	500 VRMS for one minute
Material contact	Copper alloy
Material insulator	High temp. thermoplast UL94V-0
Operating temperature	-25°C to +105°C
Max. processing temper.	240°C for 5 seconds


All dimensions in mm.

pitch	2,54
termination	
contact size	0,64
max. pincount	020


Product group
3

Variation


PCB Layout






1



2



3



Plating:
T = Sn

Variation (1,2,3)

No. of contacts

Plating contact



www.mpe-connector.de

CS17081_V2

Order code:

428-2-222-0-T-KS0

Mating series
see page

431
6-11