

T18R0HSC2

Cable Tie, 18lb. 4" max. Bun. Dia. .87" PA66HS Black 100/pk

Article Number: 111-01905

Part Number: T18R0HSC2

Type: T18R


Material: PA66HS



1. Base Data

Part No.	T18R0HSC2
Type	T18R
Color	Black (BK)
Features	HellermannTyton's heat stabilized cable ties provide excellent resistance when exposed to high heat applications.
Application	Used to bundle and secure wire and cable.
Application Method	Quick, simple application by hand or with HellermannTyton tensioning tools.

2. Product Dimensions



Min. Tensile Strength	18 lbs / 80 N
Length (L)	4 " / 100 mm
Width (W)	.10 " / 2.5 mm
Min. Ø Bundle	.06 " / 1.5 mm
Max. Ø Bundle	.87 " / 22.0 mm

4. Material and Specifications

Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL94 V2
Operating Temperature	-40 °F to +221 °F (-40 °C to +105 °C) continuous
ROHS Conformity	

Logistic and Packaging

Packaging Type	bag
Pkg. Qty.	100
Carton Qty.	10000

UPC	08930606708
-----	-------------

Miscellaneous


UL Listed (US and Canada)	Yes
UL Recognized (US and Canada)	Yes

Standard Cable Ties- Specialty Materials

T18 - T120 Series - Heat Stabilized

HellermannTyton's heat stabilized cable ties provide excellent resistance when exposed to high heat applications.

Material Data	
Material	Polyamide 6.6 heat stabilized (PA66HS)
Operating Temperature	-40 °F to +221 °F (-40 °C to +105 °C) continuous
Flammability	UL94 V2



File# E64139



File# E64139

File# E04139

File# E04139

Product Selection			Min. Tensile Strength		Length (L)	Max. Ø Bundle	Width (W)	Color	Pkg. Qty.
Article No.	Part No.	Type	lbs. (N)	in. (mm)	in. (mm)	in. (mm)			
T18S									
111-02815	T18S0HSM4	T18S	18 lbs (80)	3.27" (83)	.63" (16)	.09" (2.3)	Black	1000	
T18R									
111-01905	T18R0HSC2	T18R	18 lbs (80)	4" (100)	.87" (22)	.10" (2.5)	Black	100	
111-00476	T18R0HSM4	T18R	18 lbs (80)	4" (100)	.87" (22)	.10" (2.5)	Black	1000	
T18I									
111-02305	T18I0HSM4	T18I	18 lbs (80)	5.5" (140)	1.38" (35)	.10" (2.5)	Black	1000	
T18L									
111-00403	T18L0HSC2	T18L	18 lbs (80)	8.0" (205)	2.17" (55)	.10" (2.5)	Black	100	
111-00404	T18L0HSM4	T18L	18 lbs (80)	8.0" (205)	2.17" (55)	.10" (2.5)	Black	1000	
T30R									
111-03067	T30R0HSC2	T30R	30 lbs (135)	5.9" (150)	1.38" (35)	.14" (3.5)	Black	100	
111-03068	T30R0HSM4	T30R	30 lbs (135)	5.9" (150)	1.38" (35)	.14" (3.5)	Black	1000	
T50R									
111-04900	T50R0HSC2	T50R	50 lbs (225)	7.9" (200)	1.97" (50)	.18" (4.6)	Black	100	
111-04901	T50R0HSM4	T50R	50 lbs (225)	7.9" (200)	1.97" (50)	.18" (4.6)	Black	1000	
T50I									
111-05248	T50I0HSC2	T50I	50 lbs (225)	11.8" (300)	3.35" (85)	.18" (4.6)	Black	100	
111-05251	T50I0HSM4	T50I	50 lbs (225)	11.8" (300)	3.35" (85)	.18" (4.6)	Black	1000	
T50L									
111-05470	T50L0HSC2	T50L	50 lbs (225)	15.35" (390)	4.33" (110)	.18" (4.6)	Black	100	
111-05471	T50L0HSM4	T50L	50 lbs (225)	15.35" (390)	4.33" (110)	.18" (4.6)	Black	1000	
T120R									
111-12061	T120R0HSC2	T120R	120 lbs (535)	15.24" (387)	4.13" (105)	.30" (7.6)	Black	50	
111-12058	T120R0HSH4	T120R	120 lbs (535)	15.24" (387)	4.13" (105)	.30" (7.6)	Black	500	

Installation tools - MK7, MK7HT, MK7P, MK9, MK9HT, MK9P. MK9, MK9HT, and MK9P tools cannot be used with T18S cable ties.

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.