

Cable gland - HC-B-G-M32-PLRBK - 1407671

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

EVO plastic cable gland with bayonet locking; size M32, cable diameter: 11 - 21 mm



Product description

Plastic cable gland



Key commercial data

Packing unit	1 pc
Weight per Piece (excluding packing)	60.0 GRM
Custom tariff number	39269097
Country of origin	Poland

Technical data

Dimensions

Wrench size, union nut	30 mm
External cable diameter	11 mm ... 21 mm
Conductor sealing range	14.00 mm ... 21.00 mm

Ambient conditions

Degree of protection	IP66 (DIN IEC 60529)
	4 (UL50e / NEMA 250)
	4X (UL50e / NEMA 250)
Ambient temperature (operation)	-40 °C ... 100 °C

General

Type of the screw connection	1x M32
Cable gland material	Polyamide
Seal material	NBR
Cable seal material	NBR

Cable gland - HC-B-G-M32-PLRBK - 1407671

Technical data

General

Thread type on connection side	Bayonet
Tightening torque, union nut	7.50 Nm
Inflammability class according to UL 94	V0

Classifications

eCl@ss

eCl@ss 4.0	27141209
eCl@ss 4.1	27141209
eCl@ss 5.0	27149109
eCl@ss 5.1	27143424
eCl@ss 6.0	27149109
eCl@ss 7.0	27149109
eCl@ss 8.0	27149109

ETIM

ETIM 3.0	EC000441
ETIM 4.0	EC000441
ETIM 5.0	EC000441


UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

Drawings

Cable gland - HC-B-G-M32-PLRBK - 1407671

Dimensioned drawing



Dimensional drawing