




COIL: @ +25°C


RESISTANCE 600 Ω $\pm$ 10 %

NOMINAL VOLTAGE 26.5 VDC

MUST OPERATE 13.4 VDC

MUST RELEASE 1.5 VDC

CUSTOMER DATA SHEET



ENVIRONMENT:

VIBRATION 10 CPS TO 2000 CPS @ 20 g's

SHOCK 100 g's 6 $\pm$ 1 MS.DURATION

TEMPERATURE -65 °C TO +125 °C

CONTACT RATING: 4 AMPS 28 VDC
RESISTIVE 100,000 OPERATIONS

NOTES:

DR. R.B. 6-1-90 CK. 6-1-90 JMB



Communications
Instruments, Inc.

CUST. Hi-G
 CUST. NO. 2HA-1B-126

TYPE "HFW4A" RELAY

HFW4A1196S01