






**HEADER RIGHT ANGLE SOLDER PIN  
0.8x0.8 MM WITH THREADED  
FLANGES PIN SPACING 3.5 MM / 0.  
138 IN 100% PROTECTED AGAINST  
MISMATING  
713-1423/117-000 TO 713-1438/117-000**

|                                                      |                                                                                   |
|------------------------------------------------------|-----------------------------------------------------------------------------------|
| ITEM-NO. (ITEM-NO.)                                  | 713-1433/117-000                                                                  |
| Measured voltage (Measured voltage / V)              | 160                                                                               |
| Measured shock voltage (Measured shock voltage / kV) | 2.5                                                                               |
| Pollution degree (Pollution degree)                  | 2                                                                                 |
| Current intensity (Current intensity / A)            | 10                                                                                |
| RM (PIN SPACING / mm)                                | 3.5                                                                               |
| P (NO. OF POLES)                                     | 26                                                                                |
| Height (Height / mm)                                 | 13.3                                                                              |
| Width (Width / mm)                                   | 55.6                                                                              |
| Depth (Depth / mm)                                   | 13.5                                                                              |
| No. of connection Points (No. of connection Points)  | 26                                                                                |
| No. of potentials (No. of potentials)                | 26                                                                                |
| COLOR (COLOR)                                        | schwarz                                                                           |
| Comment (Comment)                                    | $L = ((\text{No. of poles} / 2) - 1) \times \text{Pin Spacing} + 13.6 \text{ mm}$ |
| Dimensions (Dimensions)                              | 1.2 +0.1 mm                                                                       |