

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130104-0007](#)
Status: **Active**
Overview: [Hand Lamps](#)
Description: Haztex® Hazardous and Wet Location Flood Light 100W High Pressure Sodium 16/3 SOW 30.48m (100.0')

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR39801

General

Product Family Portable Lighting
Series [130104](#)
Comments Class I, Division 1, Groups C and D; Class II, Division 2, Groups F and G; Class III
NEMA Configuration NEMA 5-15
NEMA Rating NEMA 4X
Outlet None
Overview [Hand Lamps](#)
Product Name Haztex®
Type Wide Area Lamps
UPC 78678801780
Woodhead Yes

Physical

Cord Length - Primary 30.48m (100.0')
Cord Length - Secondary N/A
Depth 403.23mm (15.875")
Duty Wet Location
Guard Included No
Guard Type N/A
Height 317.50mm (12.500")
Length 336.55mm (13.250")
Material - Globe Tempered Soda-Lime Glass
Material - Guard Cast Aluminum
Mounting Style Hand Held
Packaging Type Carton
Socket Construction N/A

Electrical

Bulb Type Metal Halide - Probe Start
Cord Type - Primary 16/3 SOOW
Lamp Type TD-6
Lamp Wattage - Maximum 100W
Lumens 9000
On/Off Switch No
Voltage (Fixture) - Maximum 120VAC 60 HZ

Material Info

Old Part Number 1070-HZ100G

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[130104Series](#)