

						UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.		APPROVALS		DATE		Amphenol Connex									
8						UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm		DRAWN		G.R.S.							04/01/08				
7	FERRULE	BRASS	NICKEL	1				CHECKED													
6	SLEEVE	TEFLON	NATURAL	1				ISSUED				PART DESCRIPTION TNC PANEL CRIMP JACK FOR RG-316 DOUBLE BRAID									
5	SPACER	BRASS	NICKEL	1				SHEET		1 OF 1											
4	CONTACT PIN	PHOS. BRONZE	GOLD	1		UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020"						PART NO. 122379									
3	BODY	BRASS	NICKEL	1				CAD FILE													
2	INSULATOR	DELTRIN	NATURAL	1				C:/122/122379.DWG				DWG. NO.		122379.DWG		REV. NC		SIZE A		SCALE NA	
1	HOUSING	BRASS	NICKEL	1																	
DESCRIPTION		MATERIAL		FINISH		QTY		DO NOT SCALE DRAWING													