


**Plug-in units type 2 with extraction handle –
front panel shielded**



Article number: 20848-485

- For 6 U, the board location can be moved 1 HP to the right by swapping the upper and lower printed board brackets. This creates space for SMD components on the left-hand side (solder side).

Delivery quantity: kit

Item	Qty	Description
1	1	Extraction handle, PPE, grey, at bottom
1a	-	Extraction handle, PPE, grey, at top
2	1	Identification plate, 1.5 mm aluminium, anodised, cut edges clean
3	1	Pivot bush, brass
4	1	Printed board bracket, diecast zinc, at bottom
4a	-	Printed board bracket, diecast zinc, at top
5	1	Printed board bracket, diecast zinc
6	1	U-front panel for extractor handle, front anodised, rear etched
7	2	Alignment pin, pressed in, stainless steel
8	2	Sleeve, PA, grey, up to 7 HP front panel width
8	4	Sleeve, PA, grey, up to 8 HP front panel width
9	2	Collar screw, cross recess/slot, nickel-plated steel, M2.5 × 12.3, up to 7 HP front panel width
9	4	Collar screw, cross recess/slot, nickel-plated steel, M2.5 × 12.3, up to 8 HP front panel width
11	1	Raised countersunk head screw, M2.5 × 8
12	1	EMC textile seal
13	2	Washer, A2.7
14	2	Pozidrive flathead screw with cross recess, nickel-plated steel, M2.5 × 10


Technical data:

Width	Height
4 HP	3 U


**Montageanweisung
Aushebegriff für
Steckbaugruppen
Trapezform**

**Assembly Instructions
Plug-in Units Type 2
with Extractor Handle C**


**Instructions de montage
poignée d'extraction
trapézoïdale pour bloc c**




3 HE Standard



3 U standard




3 U standard




A3/354


6 HE Standard



6 U standard




6 U standard




A3/355


9 HE Standard



9 U standard



9 U standard




A3/710

- ① Leiterplattenhalter, unten (bei SMD oben)
- ①a Leiterplattenhalter, oben (bei SMD unten)
- ② Leiterplattenhalter
- ③ Aushebegriff unten
- ③a Aushebegriff oben
- ④ Beschriftungsblende
- ⑤ Buchse
- ⑥ Halsschraube M 2,5 × 11
- ⑦ Nippel
- ⑧ Zylinderkopfschraube M 2,5 × 8
- ⑨ Scheibe
- ⑩ Linsensenkschraube M 2,5 × 8
- ⑪ Leiterplattenhalter mitte
- ⑫ Kontaktfeder

- ① Board holder, bottom (top for SMD)
- ①a Board holder, top (bottom for SMD)
- ② Board holder, top 3 U
- ③ Extractor handle, bottom
- ③a Extractor handle, top
- ④ Identification plate
- ⑤ Bush
- ⑥ Collar screw M 2,5 × 11
- ⑦ Sleeve
- ⑧ Cheese head screw M 2,5 × 8
- ⑨ Washer
- ⑩ Raised c/sk screw M 2,5 × 8
- ⑪ Board holder middle
- ⑫ Contact springs


- ① équerre de carte inférieure (avec CMS en haut)
- ①a équerre de carte supérieure (avec CMS en bas)
- ② équerre de carte
- ③ poignée extractrice inférieure
- ③a poignée extractrice supérieure
- ④ plaquette d'identification
- ⑤ douille
- ⑥ vis à gorge M 2,5 × 11
- ⑦ oeillet
- ⑧ vis à tête cylindrique M 2,5 × 8
- ⑨ rondelle
- ⑩ vis à tête fraisée M 2,5 × 8
- ⑪ support central de circuit imprimé
- ⑫ ressort de contact



9 HE SMD/CMS auf Kundenanfrage
möglich

9 U on request

9 U CMS possible sur demande
du client



europac PRO

Montageanweisung
EMC - Dichtung

Assembly instructions
EMC gasket

Instructions de montage
Joints EMC

