

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [15015-1051](#)
Status: **Active**
Overview: [Premo-Flex™ FFC and Etched Polyimide Jumpers](#)
Description: 0.30mm Pitch Premo-Flex™ Etched Copper Polyimide Jumper, Same Side Contacts (Type A), 0.254m Cable Length, 0.12mm Cable Thickness, 51 Circuits

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-15015-001 \(PDF\)](#)

General
Product Family Cable
Series [15015](#)
Crimp Quality Equipment Yes
Overview [Premo-Flex™ FFC and Etched Polyimide Jumpers](#)
Product Name Premo-Flex™ Jumper
UPC 884982822832

Physical
Cable Length 0.254m
Circuits (Loaded) 51
Circuits (maximum) 51
Net Weight 1.000/g
Packaging Type Bag
Pitch - Termination Interface 0.30mm
Temperature Range - Operating -40°C to +105°C
Wire Size AWG N/A
Wire/Cable Type Flat Flex Cable

Electrical
Current - Maximum per Contact 0.2A
Voltage - Maximum 50V AC/DC

Material Info

Reference - Drawing Numbers
Product Specification PS-15015-001
Sales Drawing SD-15015-001



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS

Need more information on product environmental compliance?
Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)
Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[15015Series](#)

Use With
[502598](#) 0.30mm Pitch Easy-On™
BackFlip™ Type FPC Connector

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[15015-1051](#)