

main menue



home

test & measurement

products

skills

download

online catalogue T&M

clamp-type test probes

crocodile clips

test probes

oscilloscope test probes

measuring leads

plugs

sockets

- ▶ 2 mm system
- ▶ 2 mm safety system
- ▶ 4 mm system
- ▶ 4 mm safety system

sets

miscellaneous

company

portrait

corporate association

location maps

fairs and exhibitions

jobs

imprint

terms and conditions

Home ▶ sockets ▶ sockets ▶ PKI 100

PKI 100

 datasheet for PKI 100
 article number: 930757102


View Full-Size Image



search online catalogue

Search

Search

Messetermine

No events

QR-Code



product description:	order number: 930 757-102
description:	Pole terminal with captive insulated head, which is held under constant pressure against the insulated rings by a spring. 4 mm diameter nickel-plated, brass threaded bolt with 2 mm diameter transverse hole. For non-rotating installation in switchpanels and equipment chassis with wall thickness up to 3.5 mm.
typ:	PKI 100 blau/blue
system:	4 mm system
order number:	930 757-102
color	
other color versions:	
technical data	
measurement category acc. to IEC 61010:	CAT I
type of contact:	4 mm socket (unsprung), 2 mm cross hole
type of termination:	M4 thread
rated voltage:	30 VAC / 60 VDC
rated current:	35 A
Please consider derating curve!	
contact resistance:	2 mOhm
mounting:	screw
material	
contact material:	brass
contact surface material:	nickel
housing material:	PA
environmental conditions:	
temperature range:	-25 °C to +100 °C
inflammable class:	
housing (basic material):	UL 94 V - 2
drawing	

