

► Heatsinks f.cool

► Cases f.case

▼ Connectors f.con

► Sockets

▼ PCB connectors

■ Male headers

■ Female headers

■ Direct female connectors

■ Jumpers

► IDC-connectors

► D-Sub connectors

■ Brackets for PC

► Optoelectronics

Female headers

MK 07 ...

MK 07 20 Z

for Ø 0.5 mm

Data sheet

add to request



Features

Technical Drawing

Service

Accessories / related products

grid	2.54 mm
no. of contacts	20
contact material	CuZn-alloy
surface of contact	tin-plated
surface contact / contact sleeve	Ni+4...6µm Sn
inner contact spring material	CuBe-alloy
inner contact spring surface	Ni+0,75µm Au
type internal spring	4-fingers
plugability for circuit points	□0,22x0,25mm... □0,4x0,55mm Ø0,4...0,56mm
insert depth	2.5...3.6mm
plug-in cross-section	Ø0,5mm
insertion / drawing force	1.8 N/1.4 N
shock resistance	50 g
volume resistance	≤10 mΩ
vibration resistance max.	15 g
capacity between two adjacent contacts	≤0,4 pF
nominal current	1.5 A
nominal voltage	60 V DC
test voltage	1000 V
insulating body material	PA 4.6. GF
temperature range	-40°C... +163°C (260°C/10 s)
class of inflammability	UL 94 V-0
version	Wire wrap pin, □0.635mm
specific insulation resistance	>10.0 ^{7.0} Ω·m
connection type	-
reflow solderable	yes