

FJ-20-D-06.50-4

FJ-05-D-04.80-2

(1,00 mm) .0394"

FJ SERIES

FLAT FLEXIBLE CABLE (FFC) JUMPER

SPECIFICATIONS

For complete specifications see www.samtec.com?FJ

Conductor:
Tin Plated Copper

Conductor Resistance:
300 Ω/km max

Insulation Resistance:
10 MΩ/km min
(conductor-to-conductor)

Dielectric Test:
400 VAC during 1 minute
(conductor-to-conductor)

Temperature Rating:
-30°C to +80°C

Voltage Rating:
300 VAC

Flame Resistance:
VW-1 (UL 758)




RoHS Compliant:
Yes

Mates with:
FC1, ZF1

Double or reversed ended

Variety of pin counts

Variable lengths



STRIP LENGTH	C
-2	(2,00) .079
-4	(4,00) .157

Note: Stiffener color will be blue or black at Samtec's discretion.

Note: Some sizes, styles and options are non-standard, non-returnable.