




H G F E D C B A

HOOD FIXATION SCREW
(type P0Z1)



MATERIAL:

Black hood:thermoplastic

TEMPERATURE RANGE:

-Climatic category

-55°/ +105°

PACKAGING:

Box of 50 individual sets



Tie-rop T&B



Clamp

Sheet

Screw (type P0Z1)



Dimensions are in millimeters

Shell size	Number of contacts	A	B	C	Whith clamp			Whithout clamp		Part number
					D	E		D	E	
						mini	maxi			
E	09	29.75	15.50	24.25	6.00	1.90	10.10	8.00	11.50	863093C09ASP717
A	15	29.75	15.50	32.50	6.00	1.90	10.10	8.00	11.50	----
B	25	46.50	15.50	46.00	13.50	2.60	10.10	16.00	11.50	----
C	37	46.50	15.50	60.50	13.50	2.60	10.10	16.00	11.50	----

b	20/01/98	Revisionned screw type P0Z1		--
ISS	DATE	Latest modification by : JARRY		MOD N°
Designed by: JARRY		date 06/10/97		Type of drawing: CLIENT
TITLE : UNIVERSAL PLASTIC HOOD				SHEET 1/1
SCALE: 2		---		
	FRAMATOME CONNECTORS FRANCE			This document is the property of FRAMATOME CONNECTORS FRANCE It must not be reproduced or communicated without permission in writing from the owners
	Rue Louis Breguet - BP 05 72024 LE MANS Cedex Tel. (33)02.43.78.34.00			
FORMAT A3	DRG N° C01-8655-1508			PROJECT M94D001

H G F E D C B A