






X
(without protection cap)



Loading-Plan

A blue
B orange

For Information Only
-won't be replaced when changed-

-Protection level: IP67/65
-Temperature range: -40°C ...+70°C

12	Fiber optic cable breakout Multi Mode	33 58 111 300 0004	300 ± 3	m
11	Fiber optic cable breakout Multi Mode	33 58 111 150 0004	150 ± 1,5	m
10	Fiber optic cable breakout Multi Mode	33 58 111 100 0004	100 ± 1	m
9	Fiber optic cable breakout Multi Mode	33 58 111 080 0004	80 ± 0,8	m
8	Fiber optic cable breakout Multi Mode	33 58 111 060 0004	60 ± 0,6	m
7	Fiber optic cable breakout Multi Mode	33 58 111 050 0004	50 ± 0,5	m
6	Fiber optic cable breakout Multi Mode	33 58 111 040 0004	40 ± 0,4	m
5	Fiber optic cable breakout Multi Mode	33 58 111 030 0004	30 ± 0,3	m
4	Fiber optic cable breakout Multi Mode	33 58 111 020 0004	20 ± 0,2	m
3	Fiber optic cable breakout Multi Mode	33 58 111 010 0004	10 ± 0,1	m
2	Fiber optic cable breakout Multi Mode	33 58 111 005 0004	5 ± 0,05	m
1	Fiber optic cable breakout Multi Mode	33 58 111 001 0004	1 ± 0,015	m

Cont No.	Type of cable			Part-No.		Dim. a	
		All Dimensions in mm Original Size DIN A 3		Techn. Character.		Nicht tolerierte Maß/Free size tolerances	
						FO cable assembly 1xPush Pull LC duplex Multimode 50 μm	
DRS946A	16.05.11	RO				TB 33 58 111 xxx 0004	
DRS761A	07.07.10	MS					
DRS539B							
Mod.	Dat.	Name	HARTING Electronics GmbH & Co. KG D-32339 ESPELKAMP				Blatt/ page