

B06

FEMALE HEADER PROFILE : 8.4mm STRAIGHT

PITCH: 2.54mm

SPECIFICATIONS

Material

Insulator : PBT, glass reinforced, rated UL 94V-0

Contact : Phosphor Bronze or Brass

Electrical

Current Rating : 1 Amp








Contact Resistance : 30 mΩ max.

Insulation Resistance : 3000 MΩ min.


Dielectric Withstanding Voltage : 500V AC for 1minute

Operating Temperature : -40℃ to +105℃

♦ Mating Suggestion : C15, C16, C17& C18 series.



RECOMMENDED P.C.B LAYOUT



RECOMMENDED P.C.B LAYOUT

HOW TO ORDER:

B06 - 1 - 2 - 3 - 4 - G (RoHS)

1.NO. OF CONTACT	2.CONTACT MATERIAL	3.CONTACT PLATING	4.INSULATOR COLOR
SINGLE ROW 1*2 - 1*43 DUAL ROW 2*2 - 2*43	A: BRASS B: PHOSPHOR BRONZE	T: TIN PLATED S: SELECTIVE G: GOLD FLASH A: 5u" INCH GOLD B: 10u" INCH GOLD C: 15u" INCH GOLD D: 30u" INCH GOLD	1. BLACK

GOLDSUN ELECTRONICS CO., LTD.

JAMECO NO. 308592	GOLDSUN NO. B06-1x16AG1-G-R
Description FEMALE HEADER 0.10" 16PIN SINGLE ROW	Rev. 1
UNIT: mm	SCALE: SHEET 1 OF 1
CAS No: ERN No:	