



Sample photo

Order symbol: PCM 200/150 T
Product nbr: 6016929

Description: Enclosure, PC
Remarks: Smoked transparent cover

EAN:	6418074038333
El. number:	
Finland	3421678
Denmark	8212027394
Italy	7342080
Sweden	2535451

Including: Base with metric knock-outs and TPE gasket and screws for mounting plate/DIN-rail, cover with polyamide cover screws and wing heads for cover screws.

Dimensions:		L	W	H	Rating:
mm:	255	180	150	Ingress Protection (EN 60529): IP 66/67	
inch:	10	7.1	5.9	Impact Resistance (EN 50102): IK 08	
Materials:					
Material:	PC				
Base colour:	RAL 7035				
Cover colour:	Smoked grey				
Cover screws material:	Polyamide				
Cover screws colour:	Black				
Gasket material:	TPE				
Temperatures:					
Short term:	-40 ... 120 °C				
Continuous:	-40 ... 80 °C				
Short term:	-40 ... 250 °F				
Continuous:	-40 ... 175 °F				
Accessories:					
MIV 200	Mounting plate				
MIN 15	DIN-15 Mounting rail				
MIN 20	DIN-15 Mounting rail				
MIV 15	DIN-35 Mounting rail				
MIV 20	DIN-35 Mounting rail				
FP A 200/180	Front plate				
HFP 180	Front plate hinge series				
Certificates:					
Germanischer Lloyd (GL)					
Underwriters Laboratories					
Det Norske Veritas					
Fimko					
Europe EN 50298 1998					
UL Canada					
Gost R					

