




13		12		11		10		9		8		7		6		5		4		3		2		1			
PACKAGING SEE NOTE 4 SHT 1		4-6 CKT		BULK		TAPE-N-REEL W/ VAC CAPS		N/A		BULK		TAPE-N-REEL W/ VAC CAPS		N/A		BULK		TAPE-N-REEL W/ VAC CAPS		N/A				BULK		BULK	
		8-100 CKT		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES W/ VAC CAPS		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES W/ VAC CAPS		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES W/ VAC CAPS				TUBES		TUBES	
		DIM. M±0.25 MM				6.10 (.240)				6.10 (.240)				6.10 (.240)				6.10 (.240)				8.13 (.320)				8.13 (.320)	
		PLATING				150 TIN				15 GOLD				30 GOLD								15 GOLD				30 GOLD	
		DIM. H				2.54 (.100)				2.54 (.100)				2.54 (.100)				2.54 (.100)				4.57 (.180)				4.57 (.180)	
CKTS	DIM. A		DIM. B		EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	CKTS		
	MM	IN	MM	IN																							
04	5.08	.200	2.54	.100	015-91-2040	015-91-6040	N/A	015-91-0040	015-91-6042	N/A	015-91-3040	015-91-6043	N/A	015-91-0048	015-91-5049	04											
06	7.62	.300	5.08	.200	015-91-2060	015-91-6060	N/A	015-91-0060	015-91-6062	N/A	015-91-3060	015-91-6063	N/A	015-91-0068	015-91-5069	06											
08	10.16	.400	7.62	.300	015-91-2080	015-91-6080	015-91-3087	015-91-0080	015-91-6082	015-91-3086	015-91-3080	015-91-6083	015-91-3088	015-91-0088	015-91-5089	08											
10	12.70	.500	10.16	.400	015-91-2100	015-91-6100	015-91-3107	015-91-0100	015-91-6102	015-91-3106	015-91-3100	015-91-6103	015-91-3108	015-91-0108	015-91-5109	10											
12	15.24	.600	12.70	.500	015-91-2120	015-91-6120	015-91-3127	015-91-0120	015-91-6122	015-91-3126	015-91-3120	015-91-6123	015-91-3128	015-91-0128	015-91-5129	12											
14	17.78	.700	15.24	.600	015-91-2140	015-91-6140	015-91-3147	015-91-0140	015-91-6142	015-91-3146	015-91-3140	015-91-6143	015-91-3148	015-91-0148	015-91-5149	14											
16	20.32	.800	17.78	.700	015-91-2160	015-91-6160	015-91-3167	015-91-0160	015-91-6162	015-91-3166	015-91-3160	015-91-6163	015-91-3168	015-91-0168	015-91-5169	16											
18	22.86	.900	20.32	.800	015-91-2180		015-91-3187	015-91-0180		015-91-3186	015-91-3180		015-91-3188	015-91-0188	015-91-5189	18											
20	25.40	1.000	22.86	.900	015-91-2200	015-91-6200	015-91-3207	015-91-0200	015-91-6202	015-91-3206	015-91-3200	015-91-6203	015-91-3208	015-91-0208	015-91-5209	20											
22	27.94	1.100	25.40	1.000	015-91-2220		015-91-3227	015-91-0220		015-91-3226	015-91-3220		015-91-3228	015-91-0228	015-91-5229	22											
24	30.48	1.200	27.94	1.100	015-91-2240		015-91-3247	015-91-0240		015-91-3246	015-91-3240		015-91-3248	015-91-0248	015-91-5249	24											
26	33.02	1.300	30.48	1.200	015-91-2260	015-91-6260	015-91-3267	015-91-0260	015-91-6262	015-91-3266	015-91-3260		015-91-3268	015-91-0268	015-91-5269	26											
28	35.56	1.400	33.02	1.300	015-91-2280		015-91-3287	015-91-0280		015-91-3286	015-91-3280		015-91-3288	015-91-0288	015-91-5289	28											
30	38.10	1.500	35.56	1.400	015-91-2300		015-91-3307	015-91-0300		015-91-3306	015-91-3300		015-91-3308	015-91-0308	015-91-5309	30											
32	40.64	1.600	38.10	1.500	015-91-2320		015-91-3327	015-91-0320		015-91-3326	015-91-3320		015-91-3328	015-91-0328	015-91-5329	32											
34	43.18	1.700	40.64	1.600	015-91-2340		015-91-3347	015-91-0340		015-91-3346	015-91-3340		015-91-3348	015-91-0348	015-91-5349	34											
36	45.72	1.800	43.18	1.700	015-91-2360		015-91-3367	015-91-0360		015-91-3366	015-91-3360		015-91-3368	015-91-0368	015-91-5369	36											
38	48.26	1.900	45.72	1.800	015-91-2380		015-91-3387	015-91-0380		015-91-3386	015-91-3380		015-91-3388	015-91-0388	015-91-5389	38											
40	50.80	2.000	48.26	1.900	015-91-2400	015-91-6400	015-91-3407	015-91-0400	015-91-6402	015-91-3406	015-91-3400	015-91-6403	015-91-3408	015-91-0408	015-91-5409	40											
42	53.34	2.100	50.80	2.000	015-91-2420		015-91-3427	015-91-0420		015-91-3426	015-91-3420		015-91-3428	015-91-0428	015-91-5429	42											
44	55.88	2.200	53.34	2.100	015-91-2440		015-91-3447	015-91-0440		015-91-3446	015-91-3440		015-91-3448	015-91-0448	015-91-5449	44											
46	58.42	2.300	55.88	2.200	015-91-2460		015-91-3467	015-91-0460		015-91-3466	015-91-3460		015-91-3468	015-91-0468	015-91-5469	46											
48	60.96	2.400	58.42	2.300	015-91-2480		015-91-3487	015-91-0480		015-91-3486	015-91-3480		015-91-3488	015-91-0488	015-91-5489	48											
50	63.50	2.500	60.96	2.400	015-91-2500	015-91-6500	015-91-3507	015-91-0500	015-91-6502	015-91-3506	015-91-3500	015-91-6503	015-91-3508	015-91-0508	015-91-5509	50											
52	66.04	2.600	63.50	2.500	015-91-2520		015-91-3527	015-91-0520		015-91-3526	015-91-3520		015-91-3528	015-91-0528	015-91-5529	52											
54	68.58	2.700	66.04	2.600	015-91-2540		015-91-3547	015-91-0540		015-91-3546	015-91-3540		015-91-3548	015-91-0548	015-91-5549	54											
56	71.12	2.800	68.58	2.700	015-91-2560		015-91-3567	015-91-0560		015-91-3566	015-91-3560		015-91-3568	015-91-0568	015-91-5569	56											
58	73.66	2.900	71.12	2.800	015-91-2580		015-91-3587	015-91-0580		015-91-3586	015-91-3580		015-91-3588	015-91-0588	015-91-5589	58											
60	76.20	3.000	73.66	2.900	015-91-2600		015-91-3607	015-91-0600		015-91-3606	015-91-3600		015-91-3608	015-91-0608	015-91-5609	60											
62	78.74	3.100	76.20	3.000	015-91-2620		015-91-3627	015-91-0620		015-91-3626	015-91-3620		015-91-3628	015-91-0628	015-91-5629	62											
64	81.28	3.200	78.74	3.100	015-91-2640		015-91-3647	015-91-0640		015-91-3646	015-91-3640		015-91-3648	015-91-0648	015-91-5649	64											
66	83.82	3.300	81.28	3.200	015-91-2660		015-91-3667	015-91-0660		015-91-3666	015-91-3660		015-91-3668	015-91-0668	015-91-5669	66											
68	86.36	3.400	83.82	3.300	015-91-2680		015-91-3687	015-91-0680		015-91-3686	015-91-3680		015-91-3688	015-91-0688	015-91-5689	68											
70	88.90	3.500	86.36	3.400	015-91-2700		015-91-3707	015-91-0700		015-91-3706	015-91-3700		015-91-3708	015-91-0708	015-91-5709	70											
72	91.44	3.600	88.90	3.500	015-91-2720		015-91-3727	015-91-0720		015-91-3726	015-91-3720		015-91-3728	015-91-0728	015-91-5729	72											
74	93.98	3.700	91.44	3.600	015-91-2740		015-91-3747	015-91-0740		015-91-3746	015-91-3740		015-91-3748	015-91-0748	015-91-5749	74											
76	96.52	3.800	93.98	3.700	015-91-2760		015-91-3767	015-91-0760		015-91-3766	015-91-3760		015-91-3768	015-91-0768	015-91-5769	76											
78	99.06	3.900	96.52	3.800	015-91-2780		015-91-3787	015-91-0780		015-91-3786	015-91-3780		015-91-3788	015-91-0788	015-91-5789	78											
80	101.60	4.000	99.06	3.900	015-91-2800		015-91-3807	015-91-0800		015-91-3806	015-91-3800		015-91-3808	015-91-0808	015-91-5809	80											
82	104.14	4.100	101.60	4.000	71308-0082		71308-0482	71308-0182		71308-0582	71308-0282		71308-0682	71308-1182	71308-1282	82											
84	106.68	4.200	104.14	4.100	71308-0084		71308-0484	71308-0184		71308-0584	71308-0284		71308-0684	71308-1184	71308-1284	84											
86	109.22	4.300	106.68	4.200	71308-0086		71308-0486	71308-0186		71308-0586	71308-0286		71308-0686	71308-1186	71308-1286	86											
88	111.76	4.400	109.22	4.300	71308-0088		71308-0488	71308-0188		71308-0588	71308-0288		71308-0688	71308-1188	71308-1288	88											
90	114.30	4.500	111.76	4.400	71308-0090		71308-0490	71308-0190		71308-0590	71308-0290		71308-0690	71308-1190	71308-1290	90											
92	116.84	4.600	114.30	4.500	71308-0092		71308-0492	71308-0192		71308-0592	71308-0292		71308-0692	71308-1192	71308-1292	92											
94	119.38	4.700	116.84	4.600	71308-0094		71308-0494	71308-0194																			

13		12		11				10		9		8		7		6		5		4		3		2		1			
J		PACKAGING SEE NOTE 4. SHT 1		4-8 CKT		TAPE-N-REEL W/ VAC CAPS		TAPE-N-REEL W/ VAC CAPS														BULK		BULK					
				10-100 CKT		TAPE-N-REEL W/ VAC CAPS		TAPE-N-REEL W/ VAC CAPS												TUBES		TUBES							
				DIM. M±0.25 MM		6.10 (.240)		6.10 (.240)										8.13 (.320)		13.59 (.535)									
				PLATING		30 GOLD		15 GOLD										150 TIN		150 TIN									
				DIM. H		2.54 (.100)		2.54 (.100)										4.57 (.180)		4.57 (.180)									
I		CKTS		DIM. A		DIM. B		EDP		EDP										EDP		EDP		CKTS					
				MM IN		MM IN		NUMBER		NUMBER						NUMBER		NUMBER											
H		04		5.08		.200		2.54		.100														04					
		06		7.62		.300		5.08		.200				015-91-6068										06					
		08		10.16		.400		7.62		.300				015-91-6088										08					
		10		12.70		.500		10.16		.400				015-91-6108								713088010		71308-8210		10			
		12		15.24		.600		12.70		.500																12			
		14		17.78		.700		15.24		.600		015-91-6148														14			
		16		20.32		.800		17.78		.700												713088016				16			
		18		22.86		.900		20.32		.800																18			
		20		25.40		1.000		22.86		.900																20			
		22		27.94		1.100		25.40		1.000																22			
G		24		30.48		1.200		27.94		1.100																24			
		26		33.02		1.300		30.48		1.200																26			
		28		35.56		1.400		33.02		1.300																28			
		30		38.10		1.500		35.56		1.400																30			
		32		40.64		1.600		38.10		1.500																32			
		34		43.18		1.700		40.64		1.600																34			
		36		45.72		1.800		43.18		1.700																36			
		38		48.26		1.900		45.72		1.800																38			
		40		50.80		2.000		48.26		1.900																40			
		42		53.34		2.100		50.80		2.000																42			
F		44		55.88		2.200		53.34		2.100																44			
		46		58.42		2.300		55.88		2.200																46			
		48		60.96		2.400		58.42		2.300																48			
		50		63.50		2.500		60.96		2.400																50			
		52		66.04		2.600		63.50		2.500																52			
		54		68.58		2.700		66.04		2.600																54			
		56		71.12		2.800		68.58		2.700																56			
		58		73.66		2.900		71.12		2.800																58			
		60		76.20		3.000		73.66		2.900																60			
		62		78.74		3.100		76.20		3.000																62			
E		64		81.28		3.200		78.74		3.100																64			
		66		83.82		3.300		81.28		3.200																66			
		68		86.36		3.400		83.82		3.300																68			
		70		88.90		3.500		86.36		3.400																70			
		72		91.44		3.600		88.90		3.500																72			
		74		93.98		3.700		91.44		3.600																74			
		76		96.52		3.800		93.98		3.700																76			
		78		99.06		3.900		96.52		3.800																78			
		80		101.60		4.000		99.06		3.900																80			
		82		104.14		4.100		101.60		4.000																82			
D		84		106.68		4.200		104.14		4.100																84			
		86		109.22		4.300		106.68		4.200																86			
		88		111.76		4.400		109.22		4.300																88			
		90		114.30		4.500		111.76		4.400																90			
		92		116.84		4.600		114.30		4.500																92			
		94		119.38		4.700		116.84		4.600																94			
		96		121.92		4.800		119.38		4.700																96			
		98		124.46		4.900		121.92		4.800																98			
		100		127.00		5.000		124.46		4.900																100			
		B		NO PEG VERSION (ALSO SEE SHEET 2)										SEE SHEET 1 EC NO: UCP2014-0809 DRAWN:KIPPER 2013/08/20 CHKD:JBELL 2013/08/20 APPR:FSMITH 2013/09/03		QUALITY SYMBOLS ▽=0 ▽=0 ▽=0		GENERAL TOLERANCES (UNLESS SPECIFIED)				DIMENSION STYLE MM/IN				SCALE		DESIGN UNITS INCH	
mm																		INCH		DRAWN BY KMS		DATE 1999/10/15		TITLE SALES ASSY INSULATOR DUAL ROW SMT W/BREAK-OFF .025SQ PIN GULLWING .100					
A		SIZE C		ANGULAR ±1/2°				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				MATERIAL NO. SEE TABLE		DOCUMENT NO. SD-71308-001		SHEET NO. 3 OF 6													
				THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																									
1b_frame_C_P_AM.T Rev. G 2012/01/11		12		11		10		9		8		7		6		5		4		3		2		1					

13			12		11		10		9		8		7		6		5		4		3		2		1							
PACKAGING SEE NOTE 4 SHT 1							4-8 CKT		BULK		TAPE-N-REEL W/ VAC CAPS		BULK		TAPE-N-REEL W/ VAC CAPS		BULK		TAPE-N-REEL W/ VAC CAPS		BULK		BULK		BULK							
							10-100 CKT		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES		TUBES		TUBES							
							DIM. M±0.25 MM						6.10 (.240)				6.10 (.240)				6.10 (.240)				8.13 (.320)		8.13 (.320)		8.13 (.320)			
							PLATING						150 TIN				15 GOLD				30 GOLD				150 TIN		15 GOLD		30 GOLD			
							DIM. H						2.54 (.100)				2.54 (.100)				2.54 (.100)				4.57 (.180)		4.57 (.180)		4.57 (.180)			
CKTS	DIM. A		DIM. B		DIM. C		EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	CKTS						
	MM	IN	MM	IN	MM	IN																										
04	5.08	.200	2.54	.100	----	----	015-91-1041	015-91-6044	015-91-1042	015-91-6045	015-91-1043	015-91-6046	015-91-1044	015-91-0047	015-91-1040											04						
06	7.62	.300	5.08	.200	2.54	.100	015-91-1061	015-91-6064	015-91-1062	015-91-6065	015-91-1063	015-91-6066	015-91-1064	015-91-0067	015-91-1060											06						
08	10.16	.400	7.62	.300	5.08	.200	015-91-1081	015-91-6084	015-91-1082	015-91-6085	015-91-1083	015-91-6086	015-91-1084	015-91-0087	015-91-1080											08						
10	12.70	.500	10.16	.400	7.62	.300	015-91-1101	015-91-6104	015-91-1102	015-91-6105	015-91-1103	015-91-6106	015-91-1104	015-91-0107	015-91-1100											10						
12	15.24	.600	12.70	.500	10.16	.400	015-91-1121		015-91-1122		015-91-1123		015-91-1124	015-91-0127	015-91-1120											12						
14	17.78	.700	15.24	.600	12.70	.500	015-91-1141	015-91-6144	015-91-1142	015-91-6145	015-91-1143	015-91-6146	015-91-1144	015-91-0147	015-91-1140											14						
16	20.32	.800	17.78	.700	15.24	.600	015-91-1161	015-91-6164	015-91-1162	015-91-6165	015-91-1163	015-91-6166	015-91-1164	015-91-0167	015-91-1160											16						
18	22.86	.900	20.32	.800	17.78	.700	015-91-1181		015-91-1182		015-91-1183		015-91-1184	015-91-0187	015-91-1180											18						
20	25.40	1.000	22.86	.900	20.32	.800	015-91-1201		015-91-1202		015-91-1203		015-91-1204	015-91-0207	015-91-1200											20						
22	27.94	1.100	25.40	1.000	22.86	.900	015-91-1221		015-91-1222		015-91-1223		015-91-1224	015-91-0227	015-91-1220											22						
24	30.48	1.200	27.94	1.100	25.40	1.000	015-91-1241	71308-6901	015-91-1242		015-91-1243		015-91-1244	015-91-0247	015-91-1240											24						
26	33.02	1.300	30.48	1.200	27.94	1.100	015-91-1261		015-91-1262		015-91-1263		015-91-1264	015-91-0267	015-91-1260											26						
28	35.56	1.400	33.02	1.300	30.48	1.200	015-91-1281		015-91-1282		015-91-1283		015-91-1284	015-91-0287	015-91-1280											28						
30	38.10	1.500	35.56	1.400	33.02	1.300	015-91-1301		015-91-1302		015-91-1303		015-91-1304	015-91-0307	015-91-1300											30						
32	40.64	1.600	38.10	1.500	35.56	1.400	015-91-1321		015-91-1322		015-91-1323		015-91-1324	015-91-0327	015-91-1320											32						
34	43.18	1.700	40.64	1.600	38.10	1.500	015-91-1341		015-91-1342		015-91-1343		015-91-1344	015-91-0347	015-91-1340											34						
36	45.72	1.800	43.18	1.700	40.64	1.600	015-91-1361		015-91-1362		015-91-1363		015-91-1364	015-91-0367	015-91-1360											36						
38	48.26	1.900	45.72	1.800	43.18	1.700	015-91-1381		015-91-1382		015-91-1383		015-91-1384	015-91-0387	015-91-1380											38						
40	50.80	2.000	48.26	1.900	45.72	1.800	015-91-1401		015-91-1402		015-91-1403		015-91-1404	015-91-0407	015-91-1400											40						
42	53.34	2.100	50.80	2.000	48.26	1.900	015-91-1421		015-91-1422		015-91-1423		015-91-1424	015-91-0427	015-91-1420											42						
44	55.88	2.200	53.34	2.100	50.80	2.000	015-91-1441		015-91-1442		015-91-1443		015-91-1444	015-91-0447	015-91-1440											44						
46	58.42	2.300	55.88	2.200	53.34	2.100	015-91-1461		015-91-1462		015-91-1463		015-91-1464	015-91-0467	015-91-1460											46						
48	60.96	2.400	58.42	2.300	55.88	2.200	015-91-1481		015-91-1482		015-91-1483		015-91-1484	015-91-0487	015-91-1480											48						
50	63.50	2.500	60.96	2.400	58.42	2.300	015-91-1501	015-91-6504	015-91-1502	015-91-6505	015-91-1503	015-91-6506	015-91-1504	015-91-0507	015-91-1500											50						
52	66.04	2.600	63.50	2.500	60.96	2.400	015-91-1521		015-91-1522		015-91-1523	71308-5203	015-91-1524	015-91-0527	015-91-1520											52						
54	68.58	2.700	66.04	2.600	63.50	2.500	015-91-1541		015-91-1542		015-91-1543		015-91-1544	015-91-0547	015-91-1540											54						
56	71.12	2.800	68.58	2.700	66.04	2.600	015-91-1561		015-91-1562		015-91-1563		015-91-1564	015-91-0567	015-91-1560											56						
58	73.66	2.900	71.12	2.800	68.58	2.700	015-91-1581		015-91-1582		015-91-1583		015-91-1584	015-91-0587	015-91-1580											58						
60	76.20	3.000	73.66	2.900	71.12	2.800	015-91-1601		015-91-1602		015-91-1603		015-91-1604	015-91-0607	015-91-1600											60						
62	78.74	3.100	76.20	3.000	73.66	2.900	015-91-1621		015-91-1622		015-91-1623		015-91-1624	015-91-0627	015-91-1620											62						
64	81.28	3.200	78.74	3.100	76.20	3.000	015-91-1641		015-91-1642		015-91-1643		015-91-1644	015-91-0647	015-91-1640											64						
66	83.82	3.300	81.28	3.200	78.74	3.100	015-91-1661		015-91-1662		015-91-1663		015-91-1664	015-91-0667	015-91-1660											66						
68	86.36	3.400	83.82	3.300	81.28	3.200	015-91-1681		015-91-1682		015-91-1683		015-91-1684	015-91-0687	015-91-1680											68						
70	88.90	3.500	86.36	3.400	83.82	3.300	015-91-1701		015-91-1702		015-91-1703		015-91-1704	015-91-0707	015-91-1700											70						
72	91.44	3.600	88.90	3.500	86.36	3.400	015-91-1721		015-91-1722		015-91-1723		015-91-1724	015-91-0727	015-91-1720											72						
74	93.98	3.700	91.44	3.600	88.90	3.500	015-91-1741		015-91-1742		015-91-1743		015-91-1744	015-91-0747	015-91-1740											74						
76	96.52	3.800	93.98	3.700	91.44	3.600	015-91-1761		015-91-1762		015-91-1763		015-91-1764	015-91-0767	015-91-1760											76						
78	99.06	3.900	96.52	3.800	93.98	3.700	015-91-1781		015-91-1782		015-91-1783		015-91-1784	015-91-0787	015-91-1780											78						
80	101.60	4.000	99.06	3.900	96.52	3.800	015-91-1801		015-91-1802		015-91-1803		015-91-1804	015-91-0807	015-91-1800											80						
82	104.14	4.100	101.60	4.000	99.06	3.900	71308-4082		71308-4182		71308-4282		71308-5082	71308-5182	71308-5282											82						
84	106.68	4.200	104.14	4.100	101.60	4.000	71308-4084		71308-4184		71308-4284		71308-5084	71308-5184	71308-5284											84						
86	109.22	4.300	106.68	4.200	104.14	4.100	71308-4086		71308-4186		71308-4286		71308-5086	71308-5186	71308-5286											86						
88	111.76	4.400	109.22	4.300	106.68	4.200	71308-4088		71308-4188		71308-4288		71308-5088	71308-5188	71308-5288																	

13		12		11		10		9		8		7		6		5		4		3		2		1	
J				PACKAGING SEE NOTE 4 SHT 1		4-8 CKT		BULK		TAPE-N-REEL W/ VAC CAPS		BULK		TAPE-N-REEL W/ VAC CAPS											
						10-100 CKT		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES		TAPE-N-REEL W/ VAC CAPS											
				DIM. M±0.25 MM				6.10 (.240)				6.10 (.240)													
				PLATING				30 GOLD				150 TIN													
				DIM. H				2.54 (.100)				2.54 (.100)													
I	CKTS	DIM. A		DIM. B		DIM. C		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		CKTS	
		MM	IN	MM	IN	MM	IN																		
H	04	5.08	.200	2.54	.100	----	----	015-91-1048		015-91-6047														04	
	06	7.62	.300	5.08	.200	2.54	.100	015-91-1068		015-91-6067		71308-6106		71308-6206								06			
	08	10.16	.400	7.62	.300	5.08	.200	015-91-1088		015-91-6087		71308-6108		71308-6208								08			
	10	12.70	.500	10.16	.400	7.62	.300	015-91-1108		015-91-6107		71308-6110		71308-6210								10			
	12	15.24	.600	12.70	.500	10.16	.400	015-91-1128														12			
	14	17.78	.700	15.24	.600	12.70	.500	015-91-1148		015-91-6147												14			
	16	20.32	.800	17.78	.700	15.24	.600	015-91-1168		015-91-6167												16			
	18	22.86	.900	20.32	.800	17.78	.700	015-91-1188														18			
	20	25.40	1.000	22.86	.900	20.32	.800	015-91-1208		015-91-6207												20			
	22	27.94	1.100	25.40	1.000	22.86	.900	015-91-1228														22			
G	24	30.48	1.200	27.94	1.100	25.40	1.000	015-91-1248																24	
	26	33.02	1.300	30.48	1.200	27.94	1.100	015-91-1268				71308-6126										26			
	28	35.56	1.400	33.02	1.300	30.48	1.200	015-91-1288														28			
	30	38.10	1.500	35.56	1.400	33.02	1.300	015-91-1308														30			
	32	40.64	1.600	38.10	1.500	35.56	1.400	015-91-1328														32			
	34	43.18	1.700	40.64	1.600	38.10	1.500	015-91-1348														34			
	36	45.72	1.800	43.18	1.700	40.64	1.600	015-91-1368														36			
	38	48.26	1.900	45.72	1.800	43.18	1.700	015-91-1388														38			
	40	50.80	2.000	48.26	1.900	45.72	1.800	015-91-1408		015-91-6407												40			
	42	53.34	2.100	50.80	2.000	48.26	1.900	015-91-1428														42			
F	44	55.88	2.200	53.34	2.100	50.80	2.000	015-91-1448																44	
	46	58.42	2.300	55.88	2.200	53.34	2.100	015-91-1468																46	
	48	60.96	2.400	58.42	2.300	55.88	2.200	015-91-1488																48	
	50	63.50	2.500	60.96	2.400	58.42	2.300	015-91-1508		015-91-6507												50			
	52	66.04	2.600	63.50	2.500	60.96	2.400	015-91-1528														52			
E	54	68.58	2.700	66.04	2.600	63.50	2.500	015-91-1548																54	
	56	71.12	2.800	68.58	2.700	66.04	2.600	015-91-1568																56	
	58	73.66	2.900	71.12	2.800	68.58	2.700	015-91-1588																58	
	60	76.20	3.000	73.66	2.900	71.12	2.800	015-91-1608																60	
	62	78.74	3.100	76.20	3.000	73.66	2.900	015-91-1628																62	
	64	81.28	3.200	78.74	3.100	76.20	3.000	015-91-1648																64	
	66	83.82	3.300	81.28	3.200	78.74	3.100	015-91-1668																66	
	68	86.36	3.400	83.82	3.300	81.28	3.200	015-91-1688																68	
	70	88.90	3.500	86.36	3.400	83.82	3.300	015-91-1708																70	
	72	91.44	3.600	88.90	3.500	86.36	3.400	015-91-1728																72	
D	74	93.98	3.700	91.44	3.600	88.90	3.500	015-91-1748																74	
	76	96.52	3.800	93.98	3.700	91.44	3.600	015-91-1768																76	
	78	99.06	3.900	96.52	3.800	93.98	3.700	015-91-1788																78	
	80	101.60	4.000	99.06	3.900	96.52	3.800	015-91-1808																80	
	82	104.14	4.100	101.60	4.000	99.06	3.900	71308-6082																82	
C	84	106.68	4.200	104.14	4.100	101.60	4.000	71308-6084																84	
	86	109.22	4.300	106.68	4.200	104.14	4.100	71308-6086																86	
	88	111.76	4.400	109.22	4.300	106.68	4.200	71308-6088																88	
	90	114.30	4.500	111.76	4.400	109.22	4.300	71308-6090																90	
	92	116.84	4.600	114.30	4.500	111.76	4.400	71308-6092																92	
	94	119.38	4.700	116.84	4.600	114.30	4.500	71308-6094																94	
	96	121.92	4.800	119.38	4.700	116.84	4.600	71308-6096																96	
	98	124.46	4.900	121.92	4.800	119.38	4.700	71308-6098																98	
	100	127.00	5.000	124.46	4.900	121.92	4.800	71308-6100																100	
	B	SHORT PEG VERSION (.055")																							
A																									
SEE SHEET 1 EC NO: UCP2014-0809 DRAWN:KIPPER CHKD:JBELL APPR:FSMITH		REV K5	DESCRIPTION 2013/08/20 2013/08/20 2013/09/03	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ±.--- ±.--- 3 PLACES ±.--- ±.005 2 PLACES ±0.13 ±.010 1 PLACE ±0.25 ±.--- 0 PLACE ±.--- ±.---		DIMENSION STYLE MM/IN DRAWN BY DATE KMS 1999/10/15 CHECKED BY DATE KMS 1999/10/15 APPROVED BY DATE KMS 1999/10/15		SCALE TITLE SALES ASSY INSULATOR DUAL ROW SMT W/BREAK-OFF .025SQ PIN GULLWING .100		DESIGN UNITS INCH		THIRD ANGLE PROJECTION		DOCUMENT NO. SD-71308-001		SHEET NO. 5 OF 6								
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE C	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																						
1b_frame_C_P_AM.T Rev. G 2012/01/11		12		11		10		9		8		7		6		5		4		3		2		1	

		13		12		11		10		9		8		7		6		5		4		3		2		1									
J		PEG OPTION																										J							
		NO PEG VERSION										NO PEG VERSION										LONG PEG VERSION (.130")								SHORT PEG VERSION (.055")					
		PACKAGING SEE NOTE 4, SHT 1		4-6 CKT		BULK		TAPE-N-REEL W/VAC CAPS		N/A		4-8 CKT		TAPE-N-REEL W/VAC CAPS		BULK		BULK		BULK		TAPE-N-REEL W/VAC CAPS		BULK		BULK				TAPE-N-REEL W/ VAC CAPS					
				8-100 CKT		TUBES		TAPE-N-REEL W/VAC CAPS		TUBES W/ VAC CAPS				10-100 CKT		TAPE-N-REEL W/VAC CAPS		TUBES		TUBES		TUBES		W/VAC CAPS		TUBES				BULK		TAPE-N-REEL W/ VAC CAPS			
				DIM. M±0.25 MM		6.10 (.240)								8.13(.320)		13.59(.535)		6.10(.240)		8.13(.320)		6.10 (.240)													
I		PLATING		59 TIN						59 TIN		59 TIN		59 TIN		59 TIN		59 TIN		59 TIN						59 TIN									
		DIM. H		2.54(.100)						4.57(.180)		4.57(.180)		2.54(.100)		4.57(.180)		2.54(.100)																	
KCTS		DIM. A		DIM. B		DIM. C		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		KCTS							
		MM	IN	MM	IN	MM	IN																												
H		04	5.08	.200	2.54	.100	---	---	71308-5404	71308-5504	N/A							71308-6404	71308-6504	71308-6604				71308-6706	71308-6806			04							
		06	7.62	.300	5.08	.200	2.54	.100	71308-5406	71308-5506	N/A								71308-6406	71308-6506	71308-6606			71308-6708	71308-6808			06							
		08	10.16	.400	7.62	.300	5.08	.200	71308-5408	71308-5508	71308-5608								71308-6408	71308-6508	71308-6608			71308-6710	71308-6810			08							
		10	12.70	.500	10.16	.400	7.62	.300	71308-5410	71308-5510	71308-5610			71308-5810	71308-5910				71308-6410	71308-6510	71308-6610							10							
		12	15.24	.600	12.70	.500	10.16	.400	71308-5412	71308-5512	71308-5612								71308-6412		71308-6612								12						
		14	17.78	.700	15.24	.600	12.70	.500	71308-5414	71308-5514	71308-5614								71308-6414	71308-6514	71308-6614								14						
		16	20.32	.800	17.78	.700	15.24	.600	71308-5416	71308-5516	71308-5616			71308-5816					71308-6416	71308-6516	71308-6616								16						
		18	22.86	.900	20.32	.800	17.78	.700	71308-5418		71308-5618								71308-6418		71308-6618									18					
		20	25.40	1.000	22.86	.900	20.32	.800	71308-5420	71308-5520	71308-5620								71308-6420		71308-6620									20					
		22	27.94	1.100	25.40	1.000	22.86	.900	71308-5422		71308-5622								71308-6422		71308-6622										22				
G		24	30.48	1.200	27.94	1.100	25.40	1.000	71308-5424		71308-5624		71308-5724	71308-5824				71308-6424		71308-6624									24						
		26	33.02	1.300	30.48	1.200	27.94	1.100	71308-5426		71308-5626							71308-6426		71308-6626		71308-6726							26						
		28	35.56	1.400																															