




Super-Size AkroBins®

heavy duty bins, totes, containers & small parts storage

- Large-capacity storage to improve organization
- Molded of high-impact polypropylene and unaffected by weak acids or alkalis
- Sturdy, one-piece construction is water, rust and corrosion-proof
- Guaranteed not to crack or break under normal load conditions as stated in the 1-year limited warranty
- Products made of polypropylene block copolymer are autoclavable up to 250° F
- Available in three vibrant colors – Red, Yellow and Blue

features



Anti-slide stop prevents stacked bins from shifting forward



Easy to carry with large handle molded onto back of bin




Reinforced side ribs add strength and prevent spreading when stacked



Large label area on front of bin



accessories



Window Insert optimizes interior space and keeps contents visible



Lengthwise Dividers keep items separated in the bin

Exclusively from Akro-Mils
WIDTH DIVIDERS
Create Extra Storage!



Widthwise Dividers create extra storage compartments

Super-Size AkroBins


New Ways to Super-Size & Organize

- Provide additional options to efficiently organize large items and improve workflow
- Heavy-duty bins securely stack atop each other or can sit on shelving, carts or dollies



30284 Super-Size AkroBins
23 7/8" x 8 1/4" x 7"





Super-Size AkroBins	Outside Dimensions Inches			Inside Dimensions Inches				Accessories									
	Model No.	L	W	H	L	W	H	X	Max. Cap. per Bin	Stacking Cap./= Qty. Stacked	Ctn. Qty.	Dividers*		Windows			Card Stock Holder
Width												Length	Divider Pkg. W	Qty. L	Windows	Window Pkg. Qty.	
30280	20	12⅝	6	16⅞	10⅛	5⅝	15½	200 lbs.	40 lb./10	4	—	40280 (3)	—	2	21280	2	29304
30281	20	12⅝	8	16⅞	10⅛	7⅝	15½	200 lbs.	50 lb./7	3	—	40281 (3)	—	3	21281	3	29304
30282	20	12⅝	12	16⅞	10⅛	11⅝	15½	200 lbs.	60 lb./5	2	—	40282 (3)	—	1	21282	2	29304
30283	20	18⅞	12	16⅞	16⅞	11⅝	15½	300 lbs.	150 lb./5	1	—	40282 (3)	—	1	21283	1	29304
30284	23⅞	8¼	7	20⅞	6⅝	6⅞	19⅝	200 lbs.	150 lb./5	4	41284 (2)	40286 (1)	2	4	21284	4	29304
30286	23⅞	11	7	20⅞	9⅞	6⅞	19⅞	200 lbs.	150 lb./5	4	41286 (2)	40286 (3)	2	4	21286	4	29304
30287	23⅞	11	10	20⅞	9	9⅞	19⅞	300 lbs.	150 lb./5	4	41287 (2)	40287 (3)	6	6	21287	4	29304
30288	23⅞	16½	11	20⅞	14⅝	10⅞	19⅞	300 lbs.	150 lb./5	1	41288 (2)	40287 (3)	6	6	21288	1	29304
30289	23⅞	18¼	12	20⅞	16	11⅞	19¼	300 lbs.	150 lb./5	1	41289 (2)	40289 (3)	2	1	21289	1	29304
30290	29¼	18⅞	12	26⅞	16⅞	11⅝	24⅝	300 lbs.	150 lb./5	1	—	40290 (3)	—	1	21283	1	29304
30292	29⅞	11	10	26⅞	9	9⅞	25⅞	300 lbs.	150 lb./5	4	41287 (2)	40292 (3)	6	6	21287	4	29304
30293	29⅞	16½	11	26⅞	14⅝	10⅞	25⅞	300 lbs.	150 lb./5	1	41288 (2)	40292 (3)	6	6	21288	1	29304

One color per carton: Specify Red, Blue, or Yellow. Not recommended to hang on rack or panel systems. Order in carton quantities. * () = Max. # of divider slots per bin.

Super-Size AkroBin Carts

Dimensions Inches

Model No.	Descriptions	L	W	H	Capacity lbs.	No. of Handles	Ctn. Qty.
R214CS1841	Transports six 30283 Bins	41	18	48	900	2	1
R214CS1859	Transports nine 30283 Bins	59	18	48	1350	2	1
R214CS1878	Transports twelve 30283 Bins	78	18	48	1500	2	1
R214CS2841	Transports six 30290 Bins	41	27 $\frac{1}{2}$	48	900	2	1
R214CS2859	Transports nine 30290 Bins	59	27 $\frac{1}{2}$	48	1350	2	1
R214CS2878	Transports twelve 30290 Bins	78	27 $\frac{1}{2}$	48	1500	2	1
R216CS2236	Transports sixteen 30284 Bins, six 30286 Bins, six 30287 Bins, four 30288 Bins	35 $\frac{1}{2}$	22 $\frac{1}{8}$	35	900	1	1
R216CS2836	Transports six 30292 Bins, four 30293 Bins	35 $\frac{1}{2}$	28 $\frac{1}{8}$	35	900	1	1
R216CS2239	Transports four 30289 Bins	35 $\frac{1}{2}$	22 $\frac{1}{8}$	39	900	1	1



Optional security bar available for all sizes. Bins sold separately.

Super-Size AkroBin Dollies

Dimensions Inches

Model No.	Descriptions	L	W	H	Casters	Capacity lbs.	Ctn. Qty.
RU843HR2018	Compatible with Model 30280, 30281, 30282 & 30283 Bins – Fits 1 wide	17 $\frac{1}{16}$	18 $\frac{3}{8}$	4 $\frac{1}{16}$	3" Polyolefin	500	1
RU843HR2918	Compatible with Model 30290 Bins – Fits 1 wide	26 $\frac{1}{16}$	18 $\frac{3}{8}$	4 $\frac{1}{16}$	3" Polyolefin	500	1
RU843TP2122	Compatible with Model 30286 & 30287 Bins – Fits 2 wide	20 $\frac{7}{8}$	21 $\frac{7}{8}$	4 $\frac{1}{16}$	3" Thermo-Plastic	500	1
RU843TP2227	Compatible with Model 30292 Bins – Fits 2 wide	21 $\frac{7}{8}$	26 $\frac{7}{8}$	4 $\frac{1}{16}$	3" Thermo-Plastic	500	1
RU843TP1721	Compatible with Model 30284 Bins – Fits 2 wide Compatible with Model 30288 Bins – Fits 1 wide	16 $\frac{1}{2}$	20 $\frac{7}{8}$	4 $\frac{1}{16}$	3" Thermo-Plastic	500	1
RU843TP1727	Compatible with Model 30293 Bins – Fits 1 wide	16 $\frac{1}{2}$	26 $\frac{7}{8}$	4 $\frac{1}{16}$	3" Thermo-Plastic	500	1
RU843TP1821	Compatible with Model 30289 Bins – Fits 1 wide	18 $\frac{1}{2}$	20 $\frac{7}{8}$	4 $\frac{1}{16}$	3" Thermo-Plastic	500	1

Bins sold separately.



products related products

Increase the benefits of your Super-Size AkroBins with:

- Wire Shelving Systems pgs. 36-39
- Steel Shelving Systems pgs. 40-42
- Shelf Cart pg. 47

Window Inserts

Optimize interior space and keep contents visible



Carts & Dollies



R214CS1841

AkroBin Carts

Easy organization of bulky parts in 4, 6, 9, 12 and 16 bin configurations!

- Super-Size AkroBins (sold separately) store and organize large, bulky items
- Heavy-duty frames with capacity from 900 - 1,500 lbs.



RU843TP2227

AkroBin Solid Steel Dollies

Available for efficient parts transport

Stak-N-Store Bins


heavy duty bins, totes, containers & small parts storage

NEW
color!


- The perfect way to organize heavy, bulky items
- Bins stack to form tall, stable storage arrangements on floors or standard industrial shelving
- 75 lb. weight capacity
- Colors: Red, Blue, Gray and Clear
- 13017 is also available in White




features



Large radius corners and curved upper lip add strength



Side ribs add stability when stacked



Wide hopper front allows easy access to bulky items



Large comfort grip handles



Secure Stacking

- Stack bins together to form vertical storage and picking systems



Solid Steel Dollies


- Available for efficient, easy load transport




products

Add mobility to your Stak-N-Store Bins with:


- Wire Shelving Systems pgs. 36-39
- Steel Shelving Systems pgs. 40-42
- Solid Steel Dollies pg. 50
- VERSA/Deck pg. 53
- Platform Trucks pgs. 54-57



Stak-N-Store Bins		Outside Dimensions Inches				Inside Dimensions Inches				Capacity Cu. Ft.	Ctn. Qty.
		Model No.	L	W	H	L	W	H	X		
	13014	17½	10⅞	12½	15⅞	8	12¼	13½	.98	4	
	13017	15¼	19⅞	12⅞	13⅞	17½	12¼	11½	1.7	3	
	13018	17½	16½	12½	15⅞	13¾	12¼	13½	1.6	2	

One color per carton. Specify Red, Blue, Gray or Clear. 13017 also available in White. Order in carton quantities.

Steel Dolly

Steel Dolly		Inches						
	Model No.	L	W	H	Ctn. Qty.	Capacity	Casters	Bin Compatibility
	RU843HR1617	16⅝	15¾	4½	1	900 lbs.	3" Polyolefin	13018
	RU843HR1519	19¼	14⅞	4½	1	900 lbs.	3" Polyolefin	13017




Nest & Stack Totes

heavy duty bins, totes, containers & small parts storage

- Extremely durable industrial-grade totes
- Ideal for shipping, transfer and storage applications
- NSTs stack with or without lids for storage and shipping, nest when empty
- Strong, high impact polypropylene will not rust, corrode or bend out of shape even when fully loaded
- Heavy-duty construction provides a longer service life resulting in lower replacement costs than other "budget-priced" totes
- Easy to clean, smooth surfaces are resistant to most solvents and chemicals
- NSTs are manufactured from FDA-sanctioned materials
- Optional lids protect contents from dust and damage
- Available in 9 sizes and 3 colors: Red, Blue and Gray




features



Smooth surfaces are easy to clean



Comfortable grip makes handling easy



Textured bottoms provide a no-slip grip on conveyor belts



Ribs under the lip will prevent jamming when nested

related products

Add mobility to your Nest & Stack Totes with:

- Carts pgs. 45-47
- Dollies..... pgs. 49-50
- Wire Shelving Systems pgs. 36-39



Dollies

- Available to transport containers – see pgs. 49-50



accessories




Clear Plastic Label Holders attach easily to NSTs, with or without the lid in place. Holders accommodate labels up to 3¼" x 5"



Lids feature tie holes, compatible with a variety of closures to prevent pilferage and tampering. See chart for matching lid size below

Label Holders

Model No.	Pkg. Qty.	Label Size (In.)
35010	6	3¼ x 5
35011	6	3 x 5



Nest & Stack Totes (NSTs)	Outside Dimensions Inches			Inside Dimensions Inches					NST Ctn. Qty.	Cu. Ft.	Lid Model	Ctn. Qty.
	Model No.	L	W	H	A	B	C	D				
35180	18	11	6	10	16	15¼	9¾	5¾	6	0.5	35181	6
35185	18	11	9	10	16	15½	9¾	8¾	6	0.76	35181	6
35190	19½	15½	10	14½	17	16	13¼	9¾	6	1.2	35191	6
35195	19½	15½	13	14½	17	15¾	13¾	12¾	6	1.7	35191	6
35200	19½	13½	8	12¾	17¾	16¾	11½	7¾	6	0.8	35201	6
35225	23½	19½	10	18¼	20¾	19¾	16¾	9¾	3	2	35231	3
35230	23½	19½	13	18¾	20¾	19½	16¾	12¾	3	2.6	35231	3
35240*	23½	15½	12	14¼	20¾	19¾	13	11¾	3	1.7	35241	3
35300*	29½	19½	15	18¼	26¾	25¾	16¾	14¾	3	3.7	35301	3

One color per carton. Specify color: Red, Blue or Gray. Order in carton quantities. *Made of HDPE polyethylene.



Akro-Grids

heavy duty bins, totes, containers & small parts storage


- Versatile work-in-process transfer containers
- Dividers allow subdivision of the containers down to a 1½" square compartment size
- Akro-Grids are molded with a letter/number system for easy parts tracking
- Injection-molded from polypropylene block copolymer
- Resists most solvents and chemicals
- Compatible with most racks, shelving and automated material handling equipment
- Dividers, lids and label holders sold separately
- Available in 9 sizes and 3 colors: Red, Blue and Gray



features




Divider slots allow you to create hundreds of different compartment sizes



Strong stacking rims and external ribbing provide added strength


accessories



Dividers allow subdivision of the containers down to a 1½" square compartment size. Color: Black



Clear Plastic Label Holders snap securely on any side of the container



Clear Snap-On Lids keep contents clean yet visible. Molded corner guides provide secure stacking

NEW Design!



Akro-Grids	Outside Dimensions Inches				Inside Dimensions Inches					Capacity			Accessories		
	Model No.	L	W	H	A	B	C	D	E	Bin Ctn. Qty.	Cu. Ft.	Lbs.	Long Divider*	Short Divider*	Divider Pkg. Qty.
	33105	10½	8¼	5	6⅞	9¾	9½	6½	4¾	20	.16	25	42105 (5)	41105 (7)	6
	33164	16½	10½	4	9¾	14⅝	14⅝	9¾	3¾	12	.29	20	42164 (7)	41164 (11)	6
	33166	16½	10½	6	9¾	14¾	14¾	9¾	5½	8	.44	35	42166 (7)	41166 (11)	6
	33168	16½	10½	8	9¾	14⅝	14¾	9¾	7½	6	.59	40	42168 (7)	41168 (11)	6
	33220	22¾	17¾	10	15¼	20½	19¾	14¾	9¾	2	1.66	50	42220 (11)	41220 (15)	6
	33223	22½	17¾	3	15⅞	20½	20⅞	15¾	2½	6	.47	30	42223 (11)	41223 (15)	6
	33224	22¾	17¾	4	15⅞	20⅞	20	15	3¾	6	.61	30	42224 (11)	41224 (15)	6
	33226	22¾	17¾	6	15¾	20¾	19¾	14¾	5¾	4	.96	40	42226 (11)	41226 (15)	6
	33228	22¾	17¾	8	15¾	20¾	19¾	14¾	7⅞	3	1.30	50	42228 (11)	41228 (15)	6

One color per carton. Specify Red, Blue or Gray. Order in carton quantities. *() = max # of dividers.

Clear Snap-On Lids


Model No.	Fits Grid No.	Ctn. Qty.
33011	33105	10
33061	33164, 33166, 33168	4
33023	33220, 33223, 33224, 33226, 33228	3

Label Holders

Model No.	Fits Grid No.	Pkg. Qty.
35010	Fits all except 33164, 33223, 33224	6
35011	33164, 33224	6

Adhesive Label

Model No.	Fits Grid No.	Pkg. Qty.
29203	33223	10 sheets (120 total)



Dollies

- Available to transport containers. See pgs. 49-50




Attached Lid Containers


heavy duty bins, totes, containers & small parts storage



features




Textured bottoms provide a sure grip on conveyor belts



Strong molded-in handle grips are ergonomically designed for easy lifting and carrying



Padlock eye on both ends accommodates security ties




Reinforced hinge pins for years of smooth lid operation

- ALCs stack and nest for optimal space use
- Reusable shipping, distribution, order picking, and storage containers
- Attached lids snap securely closed to protect contents from dust or damage
- Containers interwork for easy pallet loading
- See chart below for color options



ALCs		Outside Dimensions Inches			Inside Dimensions Top Inches			Inside Dimensions Bottom Inches		Capacity				
Model No.	Available Colors	L	W	H	L	W	H	L	W	Cu. Ft.	Gal.	Lbs.	Ctn. Qty.	Stack Cap./ Qty. Stacked
39085	Blue, Gray	21½	15	9	19¾	14½	8¾	18⅞	13¼	1.12	8.5	35	6	35 lbs./5
39120	Blue, Green, Red, Gray	21½	15	12½	19¾	14½	12	18⅞	13¼	1.62	12	65	6	65 lbs./5
39160	Gray	27	17	12½	25	15½	11	23½	14	2.25	16.83	100	1	100 lbs./4
39170	Blue, Gray	21½	15	17	19¾	14½	16⅞	18⅞	13¼	2.28	17	100	3	100 lbs./3
39175	Gray	24	19½	12½	22	18	11	20½	16½	2.3	17.20	80	1	80 lbs./5
39280	Gray	28	21	15½	26	19	14	25	18	3.82	28.57	100	1	100 lbs./4

Order in carton quantities. Specify color when ordering.



Dollies

- Plastic, steel and wood dollies available to transport containers. See pgs. 49-50





Straight Wall Containers

heavy duty bins, totes, containers & small parts storage

- SWCs are reusable shipping, storage, and work-in-process containers
- Straight walls provide efficient internal and external space usage
- Solid-sided containers have smooth inner walls for easy, sanitary cleaning
- Mesh-sided containers allow hot or cold air ventilation
- Injection-molded from high-density polyethylene
- Available in 4 sizes and 3 styles
- Colors: Red, Gray



37612
Mesh Side/Mesh Base



37672
Mesh Side/Solid Base




37682
Solid Side/Solid Base

products related products


Add more productivity to your Straight Wall Containers with:

- Carts pgs. 45-47
- Dollies..... pgs. 49-50
- Platform Trucks..... pgs. 54-57


features



One-inch wall thickness for secure stacking



Strong, 1" wide, stacking rims and external ribbing provide added strength



Straight walls provide efficient cubing in trucks and on pallets



Open .72 x .90 mesh pattern allows high visibility and good airflow




Dollies

- Plastic, steel and wood dollies available to transport containers. See pgs. 49-50

Straight Wall Containers (SWCs)

Model No. Mesh Side & Base	Model No. Mesh Side/Solid Base	Model No. Solid Side & Base	Outside Dimensions Inches			Inside Dimensions Top Inches			Ctn. Qty.	Stacking Capacity / Qty. Bottom Type	
			L	W	H	L	W	H		Solid	Mesh
37208	37278	37288	15 3/4	11 3/4	8 3/4	14 1/4	10 1/4	8	12	83 lbs./6	30 lbs./6
37608	37678	37688	23 3/4	15 3/4	8 3/4	22 1/4	14 1/4	8	4	83 lbs./6	45 lbs./6
37612	37672	37682	23 3/4	15 3/4	12 1/4	22 1/4	14 1/4	12	3	125 lbs./5	45 lbs./5
37616	37676	37686	23 3/4	15 3/4	16 1/4	22 1/4	14 1/4	16	2	150 lbs./4	45 lbs./4

Order in carton quantities.





Cross-Stack Akro-Tub

heavy duty bins, totes, containers & small parts storage

- Ideal for food processing and handling operations or industrial work-in-progress activities
- Industrial-grade 90° nest and stack tub
- Nesting when empty conserves storage space
- Molded-in side handles for comfortable lifting
- Manufactured from FDA-sanctioned materials
- Smooth surface is easy to clean
- Compatible with standard 36" shelving and conveyor systems
- Color: Gray



Akro-Tub & Rack

- Heavy-duty, industrial-grade nesting tub
- Tub manufactured from FDA-sanctioned materials
- Smooth surface is easy to clean
- Nests when empty to conserve storage space
- Use the Akro-Tub Rack (RA6TR4MR) to provide easy loading and transport of multiple Akro-Tubs
- 75 lb. capacity per tub
- Color: Gray



features


cross-stack akro-tub features



Stacking grooves allow stable 90° stacks



Molded-in handles for easy lifting



Extra-thick walls and reinforcing ribs provide superior strength



features




Rounded corner design adds strength to stress points




Rolled top rim forms comfortable handles



Extra-thick walls for superior strength



Ribs prevent jamming when nested

Cross-Stack Akro-Tub		Outside Dimensions Inches						Capacity Gal.	Ctn. Qty.
	Model No.	L	W	H	A	B			
	34301	17¼	11	8	13¾	7¾	3.85	6	
	34302	17¼	11	12	12¾	7	5.51	6	
	34303	23¾	17¼	8	19¾	14	9.81	6	
	34304	23¾	17¼	12	19	13¾	14.38	6	

Order in carton quantities.

Double-Sided Cross-Stack Akro-Tub Rack		Inches			
Model No.	Description	L	W	H	Rack Weight/lbs.
RACR5MR	Holds 32 (34301) Cross-Stack Akro-Tubs* or 16 (34303) Cross-Stack Akro-Tubs*	53	29	62	1000 lbs.

Order in carton quantities. *Tubs sold separately.

Akro-Tub		Inches					
Model No.	L	W	H	A	B	Capacity Gal.	Ctn. Qty.
34240	19	24 1/2	9 1/2	20 1/2	15 1/2	14.6	6

Order in carton quantities.

Akro-Tub Rack				Inches
Model No.	H	W	D	Casters
RA6TR4MR	73	24	24	4" x 2" Mold-On Rubber: 2 Rigid, 2 Swivel



Double-Sided Cross-Stack Tub Rack

- Holds 32 (34301) or 16 (34303) Cross-Stack Akro-Tubs*



Akro-Tub Rack

- Holds 6 Akro-Tubs on angle-iron slides for up to 600 lb. total capacity. Welded steel frame with 12-gauge base and bolted-on casters.*

*Akro-Tubs sold separately.

Steel Storage Cabinets

heavy duty bins, totes, containers & small parts storage

- Two cabinets fit side by side on standard 36" wide shelving
- Removable drawers are rust, corrosion and dent-proof



19228

19-Series Heavy-Duty Cabinets

Frame: 17" wide x 11" deep x 11" high with five different drawer sizes.

Drawer depth 10 1/2"

- 2 dividers per drawer



17018

17-Series Light-Duty Cabinets

Frame: 18" wide x 6" deep x 9 1/2" high. Drawer depth 5 3/4"


- 1 divider per drawer
- Removable drawers are rust, corrosion and dent-proof

features


steel storage cabinet features – 19-Series



Heavy-duty welded-steel frame with durable powder-coated finish



Label holder and transparent polystyrene window for content identification



Strong, high-impact polystyrene drawers

19-Series Drawers

- Available separately for a variety of uses
- Now available in 5 colors and 5 sizes!
- Made of high-impact polystyrene
- Drawers can be divided into as many as 8 compartments with dovetailed dividers, for customized storage

NEW colors!



Plastic Storage Cabinets


- Strong plastic cabinets organize and protect components
- Cabinets stack securely and are wall mountable
- A variety of drawer configurations provide versatile storage solutions
- Rugged, high-impact polystyrene frame
- Dividers included



10116



10124



10126



10144



10164

Storage Cabinet Hanging & Rotary Systems

Mobile Steel Cabinet Rack*

- Double-sided, mobile rail rack holds 12 of the 19-Series cabinets with as many as 336 drawers
- Supports up to 500 lbs.

Components & Quantities

- 30016 Double-Sided Rail Rack – Qty: 1
- 30424 Mobile Kit – Qty: 1
- 19-Series Cabinets – Mix or Match – Qty: 12
- 98400 Suspension Straps (Set of 2 straps) – Qty: 12 Sets

*Assembly required



Storage-Go-Round*

- Access 20 cabinets and as many as 560 drawers in less than three square feet of floor space
- Holds up to 1,000 lbs. of parts
- Accommodates 19-Series Steel Cabinets, except the 19109 (sold separately)
- Swing diameter 43 3/8"
- Stands 31" L x 31" W x 60" H

*Assembly required



19-Series Heavy-Duty Steel Cabinets

Drawer Dimensions Inches

Model No.	Description	Drawers Per Cabinet†	W	H	D	Ctn. Qty.	Drawer Model No.	Dividers 25/Pkg. Model No.
19228	Steel Storage Cabinet*	28	2 3/4	2 1/4	10 1/2	1	20228	40228
19320	Steel Storage Cabinet*	20	3 3/4	2 1/4	10 1/2	1	20320	40320
19416	Steel Storage Cabinet*	16	4	2 1/4	10 1/2	1	20416	40416
19715	Steel Storage Cabinet*	15	3 3/4	3 3/4	10 1/2	1	20715	40715
19909	Steel Storage Cabinet*	9	5 3/4	3 3/4	10 1/2	1	20909	40909
19109	Storage Cabinet w/ Locking Door	9	5 3/4	3 3/4	10 1/2	1	20909	40909

One drawer color per cabinet. Specify Red, Blue, Yellow, Gray or Black when ordering. † Two removable dividers and one label per drawer included. * Available with a locking door when ordered in quantities of 50 or more.

17-Series Light-Duty Steel Cabinets

Drawer Dimensions Inches

Model No.	Description	Drawers Per Cabinet†	W	H	D	Ctn. Qty.	Drawer Model No.	Dividers 25/Pkg. Model No.
17018	Storage Cabinet*	18	2 3/4	2 1/2	5 3/4	1	20902	40901

† One removable divider and one label per drawer included.

Plastic Storage Cabinets

Inches

Model No.	Description	L	W	H	Ctn. Qty.
10116	16-Drawer Cabinet	10 1/2	6 3/8	8 1/2	1
10124	24-Drawer Cabinet	20	6 3/8	15 13/16	1
10126	26-Drawer Cabinet	20	6 3/8	10 1/4	1
10144	44-Drawer Cabinet	20	6 3/8	15 13/16	1
10164	64-Drawer Cabinet	20	6 3/8	15 13/16	1

16-Drawer Cabinet has 8 dividers. All other cabinets have 8 small and 4 large dividers.

Additional Dividers (Plastic Cabinets)

Model No.	Description
40716	16-Pack additional dividers for small drawers
40717	6-Pack additional dividers for large drawers



Storage Cases

heavy duty bins, totes, containers & small parts storage

- Grid design in lid keeps items from spilling into other compartments
- Cases available in 3 sizes with different divider configurations
- Small and medium cases include 4 front-to-back adjustable dividers
- Large cases include 5 front-to-back adjustable dividers
- Durable clear polypropylene



05905
Large Case



05705
Small Case



05805
Medium Case



Small & Medium Cases

2 Fixed Dividers
4 Adjustable Dividers

Medium Cases

2 Fixed Dividers
4 Adjustable Dividers

Large Cases

2 Fixed Dividers
5 Adjustable Dividers



Portable Organizers



- Unique design keeps parts and equipment from migrating to other compartments when lids are shut
- Separate lid compartment holds small items
- The main compartment holds larger, bulky items
- Dividers included for both levels
- Molded-in "feet" allow case to stand upright



Roto-Shelf



- Mobile storage unit can easily be moved to different work areas, ideal for assembly components
- 19 $\frac{7}{8}$ " wide unit takes up very little floor space
- 3 shelves rotate on an independent central metal shaft
- Shelf depth – 2 $\frac{1}{8}$ ", Shelf diameter – 19 $\frac{7}{8}$ ", 75 lbs. per shelf, 300 lb. total wt. capacity



Tote Caddy



- Hand-held tool and supply caddy
- Deep compartments hold loose parts, cleaning supplies or tools for easy transport
- Molded of heavy-duty, industrial-grade polypropylene for lasting durability
- Color: Blue

Storage Cases

Dimensions Inches

Model No.	Description	L	W	H	Max. Compartments	Ctn. Qty.
05705	Small Case – 2 Fixed Dividers	8 $\frac{1}{2}$	5 $\frac{1}{2}$	1 $\frac{1}{2}$	15	12
05805	Medium Case – 2 Fixed Dividers	11	7	2 $\frac{1}{2}$	15	6
05905	Large Case – 2 Fixed Dividers	14 $\frac{1}{2}$	9 $\frac{1}{2}$	2 $\frac{1}{2}$	18	6

Order in carton quantities.

Portable Organizers

Inches

Model No.	Description	L	W	H	Max. Compartments	Ctn. Qty.
06115	Lid Storage Organizer	15	11 $\frac{1}{2}$	3 $\frac{1}{4}$	11 to 46	1
06118	Large Lid Storage Organizer	18 $\frac{1}{4}$	13 $\frac{1}{2}$	3 $\frac{1}{2}$	12 to 62	1

Order in carton quantities.

Roto-Shelf

Inches

Model No.	Description	D	H	Ctn. Qty.
02420	Roto Shelf	19 $\frac{7}{8}$	37 $\frac{1}{2}$	1

Tote Caddy

Inches

Model No.	Description	L	W	H	Ctn. Qty.
09185BLUE	Tote Caddy	13 $\frac{1}{2}$	18 $\frac{1}{2}$	9	6

Order in carton quantities