

YAE22G13

YAE22G13

YAE22G13 : 26-20 NYLON RING 46 STU



ACTIVE

RoHS compatible

BURNDY® PRODUCTS

Assistant

Add to Favorites

Email Datasheet

Print Datasheet

FCI Brings You More

Contact our sales/technical support

Sample request

Price request

Specifications

Download document

Dimensional	Physical	Approvals / Certifications	Other Features
Dimensional			
Stud Hole (Size)	#6		
	#4		
Tongue Width (in)	0.25 in.		
Wire Insulation Grip	Yes		
Insulation Diameter (Max)	0.098 in.		
Physical			
Conductor Size	20 AWG		
	22 AWG		
	24 AWG		
	26 AWG		
Element A Index	Hand Tools		
Insulation Type	Nylon		
Color Code	Amber		
Conductor Size (Range)	26 AWG to 20 AWG		
Approvals / Certifications			
Military Listed	No		
UL Listed	No		
CSA Certified	Yes		
Other Features			
Tape Mounted Catalog Number	YAE22G13M		
Tongue Type	Ring		
UPC	78181080464		
Keyword	smlterm		