



LOC	DIST	REVISIONS				
G	14	P	LTR	DESCRIPTION	DATE	APVD
			E1	REVISED PER ECO-14-016902	10NOV2014	NK DR



WIRE RANGE	Listed FILE E13288	LR7189 Certified
14-12 AWG SOLID OR STRANDED	14-12 AWG STRANDED	14-12 AWG SOLID OR STRANDED

- 1 STAMP AMP 14-12* APPROX AS SHOWN
- 2 MATERIAL: COPPER PER ASTM B-152, ANNEALED
- 3 FINISH: 0.00254 [.000100] MIN THK TIN PER ASTM B-545



5000	ON TAPE, REEL	34487-2
-	LOOSE PIECE	34487
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170° C
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: N/A
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 1.65-4.17mm² [3,260-8,230] SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 3-17-93	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK DA PATTERSON 3-17-93				
		APVD J MECKLEY 3-17-93	NAME			
		PRODUCT SPEC	TERMINAL, RING TONGUE, SOLISTRAND			
		APPLICATION SPEC				
MATERIAL		WEIGHT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
2		-	A2	00779	C=34487	-
FINISH		CUSTOMER DRAWING	SCALE	SHEET	REV	
3			8:1	1 OF 1	E1	