

Single pole, multiclamp Terminal blocks

Screw clamp   DIN 1 - 3

M 4/6.3A - 4 mm² blocks - 6 mm .238" spacing

Characteristics

		IEC NFC DIN	UL	CSA
Wire size mm ² / AWG	Solid	0.2 - 4	22-10AWG	12 AWG maxi.
	Stranded	0.22 - 4		
Voltage	V	800	600	600
Current	A	32	20	25
Rated wire size	mm ² / AWG	4 mm ²	10 AWG	12 AWG
Wire stripping length	mm / inches	9.5 mm / .37"		
Recommended torque	Nm / lb.in	0.5-0.8 Nm / 4.4-7.1 lb.in		

Selection

Description	Type	Order P/N	Packaging Weight kg
Standard block grey	 M 4/6.3A	1SNA 115 468 R2000	50
Standard block blue	 M 4/6.3A.N	1SNA 125 468 R2200	50
Standard block beige V0	 M 4/6.3A.V0	1SNA 195 468 R2100	50

Accessories

End stop		BAM	9.1 mm	1SNA 103 002 R2600	50
End section	grey	 FEM3A	3 mm	1SNA 116 576 R1500	20
	blue	 FEM3A	3 mm	1SNA 126 576 R1700	20
	yellow	 FEM3A	3 mm	1SNA 103 862 R2000	20
Assembled jumper bar (with IP20 protection)	2 poles	BJMI6	32 A	1SNA 176 663 R0000	10
	3 poles	BJMI6	32 A	1SNA 176 664 R0100	10
	4 poles	BJMI6	32 A	1SNA 176 665 R0200	10
	5 poles	BJMI6	32 A	1SNA 176 666 R0300	10
	10 poles	BJMI6	32 A	1SNA 176 667 R0400	10
Screwless jumper bar (with IP20 protection)	2 poles	 BJE6.2	32 A	1SNA 299 694 R0400	100
	3 poles	 BJE6.3	32 A	1SNA 299 695 R0500	70
	4 poles	 BJE6.4	32 A	1SNA 299 696 R0600	50
	5 poles	 BJE6.5	32 A	1SNA 299 697 R0700	40
	10 poles	 BJE6.10	32 A	1SNA 299 702 R1400	20

M 4/6.4A - 4 mm² blocks - 6 mm .238" spacing

Characteristics


		IEC NFC DIN	UL	CSA
Wire size mm ² / AWG	Solid	0.2 - 4	22-10AWG	12 AWG maxi.
	Stranded	0.22 - 4		
Voltage	V	800	600	600
Current	A	32	20	25
Rated wire size	mm ² / AWG	4 mm ²	10 AWG	12 AWG
Wire stripping length	mm / inches	9.5 mm / .37"		
Recommended torque	Nm / lb.in	0.5-0.8 Nm / 4.4-7.1 lb.in		

Selection


Description	Type	Order P/N	Packaging Weight kg
Standard block grey	 M 4/6.4A	1SNA 115 479 R2300	50
Standard block blue	 M 4/6.4A.N	1SNA 125 479 R2500	50
Standard block beige V0	 M 4/6.4A.V0	1SNA 195 479 R2400	50

Accessories

End stop		BAM	9.1 mm	1SNA 103 002 R2600	50
End section	grey	 FEM4A	3 mm	1SNA 116 629 R2200	20
	blue	 FEM4A	3 mm	1SNA 126 629 R2400	20
	yellow	 FEM4A	3 mm	1SNA 103 863 R2100	20
Assembled jumper bar (with IP20 protection)	2 poles	BJMI6	32 A	1SNA 176 663 R0000	10
	3 poles	BJMI6	32 A	1SNA 176 664 R0100	10
	4 poles	BJMI6	32 A	1SNA 176 665 R0200	10
	5 poles	BJMI6	32 A	1SNA 176 666 R0300	10
	10 poles	BJMI6	32 A	1SNA 176 667 R0400	10
Screwless jumper bar	2 poles	 BJE6.2	32 A	1SNA 299 694 R0400	100
	3 poles	 BJE6.3	32 A	1SNA 299 695 R0500	70
	4 poles	 BJE6.4	32 A	1SNA 299 696 R0600	50
	5 poles	 BJE6.5	32 A	1SNA 299 697 R0700	40
	10 poles	 BJE6.10	32 A	1SNA 299 702 R1400	20




M 4/6.3A



BAM




FEM3A




BJMI6



BJE6



M 4/6.4A



BAM



FEM4A



BJMI6



BJE6