





board layout



- ① plated holes
- ② non-metallized drillings

mating steps acc. to
PICMG MicroTCA.0 and AdvancedMC.0

The following 54 contacts are internally connected
(ground pins acc. to AdvancedMC.0): 7, 10, 13, 16, 19, 22, 25, 28,
31, 34, 37, 40, 43, 46, 49, 52, 55, 58, 61, 64, 67, 70, 73, 76, 79,
82, 85, 86, 89, 92, 95, 98, 101, 104, 107, 110, 113, 116, 119, 122,
125, 128, 131, 134, 137, 140, 143, 146, 149, 152, 155, 158, 161, 164

All Dimensions in mm Original Size DIN A 3			Techn. Character.			Nicht tolerierte Maß/Free size tolerances	
				Dat.	Name	2:1	Piggyback, Plug-Connector Basic Side, 170 pole solder
			Detail.	17.03.10	HL.		
			Insp.	17.03.10	Li		
			Stand.				
36045	17.08.10	HL.	HARTING Electronics GmbH & Co. KG D-32339 ESPELKAMP			TB 16 25 170 1301 000	Blatt/ page
35378	20.05.10	HL.					
35565							
Mod.	Dat.	Name				Sub.	