

RJ45 sleeve housings - VS-08-T-RJ45/IP 67 - 1688696

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



RJ45 sleeve housing, IP67, for pin insert VS-08-ST-RJ45, with push-pull interlocking for panel mounting frames, for cable cross section 5.0 mm ... 6.5 mm



Key commercial data

Packing unit	1
Minimum order quantity	1
Catalog page	Page 170 (PC-2007)
GTIN	 4 017918 863616
Custom tariff number	85472000
Country of origin	GERMANY

Technical data

Mechanical characteristics

Insertion/withdrawal cycles	≥ 1000
External cable diameter	5 mm ... 6.5 mm
Cable exit	Straight
Color	gray
Tightening torque max.	2.5 Nm
Ambient temperature (operation)	-40 °C ... 80 °C

Material data

Inflammability class according to UL 94	V0
Housing material	PA
Material, O-ring	FPM
Cable seal material	NBR
Degree of protection	IP67

RJ45 sleeve housings - VS-08-T-RJ45/IP 67 - 1688696

Classifications

eclass

eCl@ss 4.0	27140816
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260705
eCl@ss 7.0	27440309

etim

ETIM 2.0	EC000764
ETIM 3.0	EC001121
ETIM 4.0	EC001121
ETIM 5.0	EC001121

unspsc

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

Accessories

Accessories

Protective covers

Protective covers - VS-SCRJ-PC - 1653757



IP67 protective cover, for covering the male inserts in the sleeve housings IP67, VS-SCRJ-..., VS-04-..., VS-06-... and VS-08-...

RJ45 male insert - VS-08-ST-RJ45 - 1688573




RJ45 pin insert, CAT5e, 8-pos., shielded, IDC connection method, for litz wires AWG 26 and solid wires AWG 26 ... 24

Drawings

RJ45 sleeve housings - VS-08-T-RJ45/IP 67 - 1688696

Dimensioned drawing



RJ45 sleeve housing IP67

© Phoenix Contact 2012 - all rights reserved
<http://www.phoenixcontact.com>