



Units:mm



PIN ASSIGNMENT:

P1	P2	P3	COLOR
1	1	1	RED
2	1	1	WHITE
3	2	2	DRAIN(RED)
		2	DRAIN(WHITE)

Electrical test:
1. 100% short, open, miswire test
2. Conduct resistance: 5 Ohm(max)
3. Insulation resistance: 10Mohm(min)
4. dielectric test: DC 300V



⑪	TIE	2	BLACK L=120mm
⑩	PE BAG	1/5	CLEAR SIZE: 280*330*0.05mm PRINT BLACK*MADE IN CHINA*+*5PCS*
⑨	PE BAG	1	CLEAR SIZE: 150*280*0.05mm PRINT BLACK*MADE IN CHINA*+*1PC*
⑧	TUBE	3	HEAT SHRINK TUBE BLACK OD1.5*10mm
⑦	S/R	1.5g	BLACK PVC 40P (Mould NO.:SR-048)
⑥	IN JACKET	0.8g	CLEAR LD-PE (Mould NO.:NM-006)
	OUT JACKET	3.3g	PVC-40P RED(RD-35),(Mould NO.:WM-009)
⑤	IN JACKET	0.8g	CLEAR LD-PE (Mould NO.:NM-006)
	OUT JACKET	3.3g	PVC-40P WHITE(W-100)(Mould NO.:WM-009)
④	OUT JACKET	3.0g	BLACK PVC-40P (Mould NO.:WM-020)
③	CABLE	1	NOUL TC(100.10)*S(280.10)*2F JACKET BLACK OD2.8*5.6mm
②	CONN	2	RCA PLUG MALE BLOSSOM TYPE NI-PLATED INSULATOR COLOR:BROWN
①	CONN	1	3.55T MALE Tray6.0mm L=26mm MOLD TYPE NI-PLATED INSULATOR COLOR:BLACK
NO.	NAME	QTY	SPECIFICATION

Cnc Tech, LLC
Industrial Cable and Connector Technology

DRAWN BY	LICHENG	DRAWING NO.	
CHECKED BY		CUSTOMER	
APPROVAL BY		ITEM NO.	770-10043-00500
DECIDE BY		DATE	2012-12-17
VERSIONS/EDITION	A/0	PROJECTION	