

1


2

3

4


A

A




B

B



C

C

**Specification:****Material:**

Insulator:PBT, rated UL94V-0

Contacts: Copper Alloy

Shell: Steel

Contact Plating

Underplate: 40u" Nickel

Contact Area:1u"~30u" selective gold

Solder Tails Area: 100u" Tin/Lead

Shell Plating

N=Nickel over copper alloy

Electrical:

Operation Voltage: 25

Operating Temperature: -5°C to +105°C

1.Series No.**2.Type:** A=Standard**3.Contact Number:** 14.24.36.50**4.Contact Type:** F=Female**5.Contact Plating:** G=Gold Flash

S=Selective Gold

A=5u" Gold (Selective)

B=10u" Gold(Selective)

C=15u" Gold(Selective)

D=30u" Gold(Selective)

6.Shell Plating:N=Nickel**7.Process Option:** A=Standard Type
(Male+Metal Cover)**8.Fill it with "0"****9.Fill it with "0"****10.Insulator Color:** 2=Blue

3=Black

Description

Name :

A57-XXF

Centronic Solder

ASSMANN
Electronic Components

Position	A	B	C	D
14F	25.20	36.00	43.90	22.70
24F	36.00	46.80	54.70	33.50
36F	48.90	59.70	67.70	46.60
50F	64.10	74.90	82.80	61.70

RoHS
Compliant

THIS DRAWING IS UNPUBLISHED

© Copyright 2005 by Assmann Electronic Components All International Rights Reserved

This drawing is a controlled document for Assmann Electronics, Inc. It is subject to change and the controlling engineering organization should be contacted for the latest revision.

1

2

3

4

D

D