


UNIT:MM




PIN ASSIGNMENT:

P1	P2
1	8
2	3
3	2
4	20
5	7
6	6
7	4
8	5
9	22
SHELL	SHELL

Electrical test:

- 1.100% short,open,miswire test
- 2.Conduct resistance:2 Ohm(max)
- 3.Insulation resistance:5Mohm(min)
- 4.dielectric test:DC 300V



1PC/PE BAG

①	PE BAG	1/10	CLEAR SIZE: 170*250*0.05mm PRINT BLACK"MADE IN CHINA""+"10PCS"
⑧	PE BAG	1	CLEAR SIZE: 80*100*0.05mm PRINT BLACK"MADE IN CHINA" +"1PC"
⑦	NUT	2	UNT:#4-40UNC 4.75*5.9mm NICKEL PLATED
⑥	SCREW	4	THUMB SCERW #4-40UNC L21mm MOLD BEIGE(IV-29#)
⑤	OUT JACKET	30g	40P PVC BEIGE(IV-29#)
④	IN JACKET	7.8g	CLEAR LD-PE
③	CABLE	455mm	UL1007 26AWG COLOR BLACK L1=45mm*9PCS L2=50mm*1PCS.
②	CONN	1	DB25P MALE SOLDER TYPE PIN G/F,BLUE INSULATION SHELL-NICKEL,
①	CONN	1	DB9P MALE SOLDER TYPE G/F ,BLUE INSULATION SHELL-NICKEL,
NO.	NAME	Q'TY	SPECIFICATION

CnC Tech, LLC			
Industrial Cable and Connector Technology			
DRAWN BY	H S F	DARWING NO.	VG/LJQ-094-093
CHECKED BY		CUSTOMER	C n C
APPROVAL BY		ITEM NO.	460-BE-9M25M
DECIDE BY		DATE	2015-04-07
VERSIONS/EDITEON	A/0	PROJECT	