


**109-00094**

Q Tie, 7.7" Long, 18lb Tensile Strength, PA66HS, Black, 100/pkg

Article Number: 109-00094



Part Number: 109-00094

Type: Q18L

Base Data

Part No.	109-00094
Type	Q18L
Color	Black (BK)
Features	• Open-head design with easily detectable slot opening allows for swift and easy insertion • Pre-lock feature allows for a temporary hold • The large ribbed tail permits an ergonomic installation • Two rails on the strap ensure guidance through the cable tie head
Identification Plate Position	none
Releasable Closure (Yes/No)	No
Tie Closure	plastic pawl
Variant	Inside Serrated

Product Dimensions

Min. Tensile Strength	18.0lbs / 80N
Length (L)	7.7" / 195mm
Width (W) (imperial)	0.1"
Width (W)	2.6mm
Min. Ø Bundle	0.06" / 2.0mm
Max. Ø Bundle	2.0" / 50.0mm
Thickness	1.0mm

Material and Specifications

Material	Polyamide 6.6 heat stabilized (PA66HS)
-----------------	--

Flammability	UL94 V2
Halogenfree	YES
Material Specification	RoHS
Operating Temperature	-40 °F to +221 °F (-40 °C to +105 °C)
ROHS Conformity	

Logistic and Packaging

Packaging Type	bag
Pkg. Qty.	100
Carton Qty.	25000
EAN code	4031026412337

© HellermannTyton North America 2011 | [TS16949](#), [ISO 9001](#) and [ISO 14001 Certified](#)
7930 N. Faulkner Rd. Milwaukee, WI 53224-9517 | Fax: 800-848-9866 | Phone: 800-537-1512