





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		E	REVISED PER ECR-12-013518	26NOV2012	KH	PD


- 1
- CONTINUOUS STRIP ON REELS
- 2
- ACCEPTS #18-#14 AWG WIRE SIZE
CRIMP WIDTH, .120, F TYPE
- 3
- INSULATION RANGE IS .120-.170 DIA
CRIMP WIDTH, .180, F OR O TYPE
- 4
- MATING TAB THK IS .032±.001.
- 5
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING
PER D.RENAUD/D.SINISI



SECTION C-C



SECTION A-A



SECTION B-B

5	OBSOLETE	-	1217917-2
		.000080 MIN TIN	1217917-1
		FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	JR RUTH	22JAN03	 TE Connectivity					
		CHK	P DESANTIS	11NOV03						
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	P DESANTIS	22JAN03	NAME				
	0 PLC ± -		PRODUCT SPEC							
	1 PLC ± -		—							
	2 PLC ± -		APPLICATION SPEC							
	3 PLC ± -		—							
	4 PLC ± .010				SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
	4 PLC ± -				A2	00779	C-1217917			
	ANGLES ± ±									
MATERIAL	FINISH	WEIGHT	—					—		
BRASS	SEE TABLE	CUSTOMER DRAWING		SCALE		1:1	SHEET	1 of 1	REV	E