



Ring Terminals

159-1201, 159-1202, 159-1203,
159-1204, 159-1205, 159-1206



Ring Terminals

159-1201, 159-1202, 159-1203, 159-1204, 159-1205, 159-1206



Dimensions: In.

SPECIFICATIONS	
Wire range:	12-10 AWG
Maximum electric current:	48 ampere
Maximum electric rating:	75°C 600 volts max.
Insulation color:	yellow
Terminal material:	copper, thickness: .039 (1.0mm)
Insulation material:	vinyl

Mouser Stock No.	Stud Size	Dimensions (In.)					
		W	L	F	B	D	C
159-1201	#6	.283	.882	.232	.492	.504	.134
159-1202	#8	.374	1.039	.327	.492	.504	.134
159-1203	#10	.374	1.039	.327	.492	.504	.134
159-1204	1/4	.472	1.150	.433	.492	.504	.134
159-1205	5/16	.591	1.327	.540	.492	.504	.134
159-1206	3/8	.591	1.327	.540	.492	.504	.134

Date Last Revised: 6-23-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300742