


BNC Series


ELBOW PLUGS

Solder center contact, clamp outer



Impedance	Cable group ①	Part Number ②	
50 ohm	010	B35 B02 • 010 X99	Captive contact, pressure sleeve cable clamp
50 ohm	010	B35 B12 • 010 X99	Captive contact, V groove gasket, braid clamp
50 ohm	022	B35 B02 • 022 X99	Captive contact, pressure sleeve cable clamp
75 ohm	012	B37 B02 • 012 X99	Captive contact, pressure sleeve cable clamp
75 ohm	022	B37 B02 • 022 X99	As above
75 ohm	025	B37 B02 • 025 X99	As above
75 ohm	025	B37 B12 • 025 X99	Captive contact, V groove gasket, braid clamp
75 ohm	052	B37 B02 • 052 X99	Captive contact, pressure sleeve cable clamp
75 ohm	062	B37 B02 • 062 X99	As above

Crimp center contact, crimp outer



Impedance	Cable group ①	Part Number ②	Crimp tool ③
50 ohm	010	B35 B28 • 010 X99	30040 or 30039
50 ohm	022	B35 B28 • 022 X99	30040 or 30039
50 ohm	060	B35 B28 • 060 X99	30040 or 30039
75 ohm	012	B37 B28 • 012 X99	30040 or 30039
75 ohm	022	B37 B28 • 022 X99	30040 or 30039
75 ohm	A25	B37 B28 • A25 X99	30040 or 30039
75 ohm	B25	B37 B28 • B25 X99	30040 or 30039

① For cable group to cable type cross reference refer to page 200.

② Replace the • in the part number with required plating code, see page 3 for details.

③ Crimp tool 30039 requires separate dies, for all details on tooling, see page 194.

Please contact the Sales Office for any uncataloged requirements.

All measurements are in millimeters unless otherwise specified.

M/A-COM, Inc.

North America: Tel. (800) 366-2266
Fax (800) 618-8883

Asia/Pacific: Tel. +85 2 2111 8088
Fax +85 2 2111 8087

Europe: Tel. +44 (1344) 869 595
Fax +44 (1344) 300 020