

UTS Series



Crimp contacts

Standard version



Contact size	Type	Wire size		Part number		Max wire Ø	Max insulator Ø	Color band		Plating available
		AWG	mm²	Male	Female			Front	Rear	
#20 Ø1 mm	Machined	26-24	0.13-0.20	RM24W3-	RC24W3-		1.58 max	-	-	K
	S&F	26-24	0.13-0.25	SM24W3S26 (1) SM24WL3S26 (2)	SC24W3S25 (1) SC24WL3S25 (2)		0.89-1.58	-	-	S25, S26
	Machined	22-20	0.32-0.52	RM20W3-	RC20W3-		1.58 max	-	-	K
	S&F	22-20	0.35-0.5	SM20W3S26 (1) SM20WL3S26 (2)	SC20W3S25 (1) SC20WL3S25 (2)		1.17-2.08	-	-	S25, S26
	Machined	20-18	0.50-0.93	RM18W3-	RC18W3-		2.10 max	-	-	K
#16 Ø1.6 mm	Machined	30-28	0.05-0.08	RM28M1-	RC28M1-	0.55	1.1	-	-	K, J, T
	Machined	26-24	0.13-0.2	RM24M9-	RC24M9-	0.8	1.6	Red	-	K, J, T
	S&F	26-24	0.13-0.25	SM24M1- (1) SM24ML1- (2)	SC24M1- (1) SC24ML1- (2)	0.89-1.28		-	-	S31, S18, TK6
	Machined	22-20	0.32-0.52	RM20M13-	RC20M13-	1.18	1.8	Black	-	K, J, T
				RM20M12-	RC20M12-		2.2	Blue	-	
	S&F	22-20	0.35-0.5	SM20M1- (1) SM20ML1- (2)	SC20M1- (1) SC20ML1- (2)	1.17-2.08		-	-	S31, S18, TK6
	Machined	20-16	0.52-1.5	RM16M23-	RC16M23-	1.8	3.2	-	-	K, J, T
	S&F	18-16	0.8-1.5	SM16M1- (1) SM16ML1- (2)	SC16M1- (1) SC16ML1- (2)	3.0		-	-	S31, S18, TK6
	S&F	18-16	0.8-1.5	SM16M11- (1) SM16ML11- (2)	SC16M11- (1) SC16ML11- (2)	2.0-3.0		-	-	S31, S18, TK6
	Machined	16-14	1.5-2.5	RM14M50-	RC14M50-	2.05	3.2	-	-	K, J, T
	Machined	16-14	1.5-2.5	RM14M30-	RC14M30-	2.28	3.2	-	-	K, J, T
	S&F	14	2.0	SM14M1- (1) SM14ML1- (2)	SC14M1- (1) SC14ML1- (2)	3.2		-	-	S31, S18, TK6
#12 Ø2.4 mm	Machined	22	0.13-0.4	8291 1457N-	8291 1456-	-	4.9	-	-	A, K
		20	0.5	8291 1459N-	8291 1458-					
		18	0.75-1.0	8291 1461N-	8291 1460-					
		16	1.5	8291 1463N-	8291 1462-					
		14	2.5	8291 1465N-	8291 1464-					
		12	4	8291 1467N-	8291 1466-					
#8 Ø3.6 mm	Machined	16	1.5	8291 3601-	8291 3600-	-	6.5	-	-	A
		14	2.5	8291 3603-	8291 3602-					
		12	4	8291 3605-	8291 3604-					
		10	6.0	8291 3607-	8291 3606-					
		8	10.0	8291 3609-	8291 3608-					

(1) contact reeled
(2) loose contact