

ALPHA WIRE COMPANY

CUSTOMER PRODUCT SPECIFICATION

Part Number: FIT221V
Page 1 of 2 Pages

Issue: 4
Issue Date: 12/31/2008
Effective Date: 3/1/2009

A. Construction

- | | |
|--------------------|--|
| 1) Tubing Type | Heat Shrinkable Tubing |
| 2) Tubing Material | Cross Linked Polyolefin |
| 3) Color(s) | BLACK, WHITE, RED, YELLOW, GREEN, BLUE |

Part Number	Minimum Supplied ID (In)	Maximum Recovered ID (In)	Nominal Recovered Wall Thickness (In)
FIT221V-3/64	0.046	0.023	0.016
FIT221V-1/16	0.063	0.031	0.017
FIT221V-3/32	0.093	0.046	0.020
FIT221V-1/8	0.125	0.062	0.020
FIT221V-3/16	0.187	0.093	0.020
FIT221V-1/4	0.250	0.125	0.025
FIT221V-3/8	0.375	0.187	0.025
FIT221V-1/2	0.500	0.250	0.025
FIT221V-3/4	0.750	0.375	0.030
FIT221V-1IN	1.000	0.500	0.035
FIT221V-1 1/2	1.500	0.750	0.040
FIT221V-2IN	2.000	1.000	0.045

B. Industry Approvals

- | | |
|-----------------------------------|--|
| 1) UL | Standard 224
VW-1 |
| 2) CSA International | Standard 198 |
| 3) Other | AMS-DTL-23053/5 Class 1 & 3
REACH Regulation (EC 1907/2006) |
| 4) EU Directive 2002/95/EC(RoHS): | All materials used in the manufacture of this part are in compliance with EU Directive 2002/95/EU regarding the restriction of use of certain hazardous substances in electrical and electronic equipment. Consult Alpha Wire's web site for compliance Date of Manufacture. |

C. Physical & Mechanical Properties

- | | | |
|----------------------------------|------------------------------|---------------|
| 1) Temperature Range | -55 to 135°C | |
| 2) Shrink Ratio | Approximately 2:1 | |
| 3) Full Recovery Temperature | 121°C | |
| 4) Minimum Shrink Temperature | 90°C | |
| 5) Tensile Strength | 1500psi, Min | ASTM D638 |
| 6) Elongation | 200%, Min | ASTM D638 |
| 7) Low Temperature Flex(-55°C) | no cracking | AMS-DTL-23053 |
| 8) Heat Resistance(175°C,168hrs) | 100% Elongation, Min | ASTM D638 |
| 9) Heat Shock(250°C,4hrs) | no cracking | AMS-DTL-23053 |
| 10) Secant Modulus | 2.5x10 ⁴ psi, Min | ASTM D882 |
| 11) Longitudinal Change | +/-5% | AMS-DTL-23053 |
| 12) Specific Gravity(Colors) | 1.35, Max | ASTM D792 |
| Specific Gravity(Clear) | 1.00, Max | |
| 13) Shelf Life | 5 Years @ 0 to 35°C | |

D. Electrical Properties

- | | | |
|------------------------|--------------------------------|-----------|
| 1) Dielectric Strength | 500 V/mil, Min | ASTM D876 |
| 2) Volume Resistivity | 1x10 ¹⁴ ohm-cm, Min | ASTM D876 |

E. Chemical Properties

- | | | |
|----------------------------------|---------------|---------------|
| 1) Water Absorption | 0.50%, Max | ASTM D570 |
| 2) Fluid Resistance(23°C,24 Hrs) | 1000 PSI, Min | AMS-DTL-23053 |

Although Alpha Wire Company ("Alpha") makes every reasonable effort to ensure their accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

ALPHA WIRE COMPANY
CUSTOMER PRODUCT SPECIFICATION

Part Number: FIT221V
Page 2 of 2 Pages

Issue: 4
Issue Date: 12/31/2008
Effective Date: 3/1/2009

- | | | |
|----------------------------|-----------|-----------|
| 3) Vacuum Outgassing - CVC | 0.1%, Max | ASTM E595 |
| 4) Halogen Free | No | |
| 5) Lead Free | No | |

F. Other

- 1) Packaging
 - a) FIT221V-3/64
3X1000 FT, 1000 FT, 250X4 FT, 25X4 FT, 40X6 IN
 - b) FIT221V-1/16
3X1000 FT, 1000 FT, 250X4 FT, 25X4 FT, 36X6 IN
 - c) FIT221V-3/32
3X500 FT, 250X4 FT, 500 FT, 25X4 FT, 32X6 IN
 - d) FIT221V-1/8
3X500 FT, 250X4 FT, 500 FT, 25X4 FT, 28X6 IN
 - e) FIT221V-3/16
250X4 FT, 2X500 FT, 500 FT, 25X4 FT, 24X6 IN
 - f) FIT221V-1/4
250X4 FT, 2X250 FT, 250 FT, 25X4 FT, 20X6 IN
 - g) FIT221V-3/8
250X4 FT, 2X200 FT, 200 FT, 25X4 FT, 16X6 IN
 - h) FIT221V-1/2
200X4 FT, 2X150 FT, 150 FT, 5X4 FT, 14X6 IN
 - i) FIT221V-3/4
125X4 FT, 250 FT, 5X4 FT, 12X6 IN
 - j) FIT221V-1IN
75X4 FT, 250 FT, 5X4 FT, 8X6 IN
 - k) FIT221V-1 1/2
125 FT, 5X4 FT, 5X6 IN
 - l) FIT221V-2IN
125 FT, 5X4 FT, 3X6 IN

Although Alpha Wire Company ("Alpha") makes every reasonable effort to ensure their accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.