

## VGA + Audio over Cat5 Extender 2-Port Transmitter

MODEL NUMBER: **B132-002A**



### Description

Tripp Lite's B132-002A allows you to split a single VGA Video and Audio signal into 2. Along with a [B132-100A](#) or [B132-100A-WP-1](#) remote receiver unit, you can extend a 1920 x 1440 (60Hz) Video and Audio signal up to 500 ft., or a 1024 x 768 (60Hz) Video and Audio signal up to 1,000 ft., when using 24Awg, Solid Wire Cat5e/6 cable, such as Tripp Lite's [N022-01K-GY](#) (Cat5) and [N222-01K-GY](#) (Cat6). For optimal image quality between 500 and 1,000 ft., use Zero-Skew cable, such as Tripp Lite [P524-01K](#). Includes mounting hardware that allows unit to be wallmounted, rackmounted or pole mounted. Ideal for digital signage situations, such as retail, schools, churches, etc.

### Features

- Splits a single VGA Video and Audio signal into 2
- When used with a [B132-100A](#) or [B132-100A-WP-1](#) remote receiver unit, you can extend a 1920 x 1440 (60Hz) Video and Audio signal up to 500 ft., or a 1024 x 768 (60Hz) Video and Audio signal up to 1,000 ft., when using 24Awg, Solid Wire Cat5e/6 cable, such as Tripp Lite's [N022-01K-GY](#) (Cat5) and [N222-01K-GY](#) (Cat6)
- For optimal image quality between 500 and 1,000 ft., use Zero-Skew cable, such as Tripp Lite [P524-01K](#)
- Includes mounting hardware that allows unit to be wallmounted, rackmounted or pole mounted.
- Ideal for digital signage situations, such as retail, schools, churches, etc.
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### Highlights

- Splits a single VGA Video and Audio signal into 2
- Extends a 1920 x 1440 (60Hz) Video and Audio signal up to 500 ft., or a 1024 x 768 (60Hz) Video and Audio signal up to 1,000 ft., when using 24Awg, Solid Wire Cat5e/6 cable, such as Tripp Lite's [N022-01K-GY](#) (Cat5) and [N222-01K-GY](#) (Cat6)
- For optimal image quality between 500 and 1,000 ft., use Zero-Skew cable, such as Tripp Lite [P524-01K](#)
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### Package Includes

- 2 Port Extender/Splitter local (Transmitter) unit
- Mounting hardware
- External power supply (Input: 100-240V, 50/60Hz, 0.5A Output: 5V, 2A)
- Owner Manual

## Specifications

| General Info  |                                 |
|---------------|---------------------------------|
| Product Group | SPLITTERS, SWITCHES & EXTENDERS |
| OVERVIEW      |                                 |
| Cable Type    | VGA                             |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

|                                     |                         |
|-------------------------------------|-------------------------|
| Display Style                       | Splitter                |
| <b>PHYSICAL</b>                     |                         |
| Shipping Weight (lbs.)              | 1                       |
| Shipping Weight (kg)                | 0.45                    |
| Unit Dimensions (hwd / in.)         | 1 x 2.5 x 3.6           |
| Unit Dimensions (hwd / cm)          | 2.54 x 6.35 x 9.14      |
| Unit Weight (lbs.)                  | 0.45                    |
| Unit Weight (kg)                    | 0.20                    |
| Color                               | Black                   |
| <b>CONNECTIONS</b>                  |                         |
| Connector A                         | HD15 (FEMALE)           |
| Connector B                         | 3.5MM (FEMALE)          |
| Connector C                         | RJ45 (FEMALE) (X2)      |
| <b>WARRANTY</b>                     |                         |
| Product Warranty Period (Worldwide) | 1-year limited warranty |

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.