



AC

UF15KC series



Size: (172 x 150 x 55 mm)
6.77 x 5.91 x 2.17 inches

Operating voltage (VAC): 115 or 230
Construction: aluminum die cast frame; UL94V-0 PBT impeller
Bearing option: motor quality ball bearings
Motor: permanent split capacitor
Air flow: exhaust over struts
Connection: terminal or 22 AWG lead wire
Protection: thermal
Option: IP55; IP55 + salt fog



Model No.	Rated Voltage V	Freq. HZ	Input Power W	Rated Cur. A	Locked Cur. A	Speed RPM	Air Volume		Max. Static Pressure (H ₂ O)		Sound Noise db	Weight lbs
							M ³ /Min.	CFM	MM	INCH		
UF15KC12 - __H	115	60	38	0.34	0.76	3400	8.3	293	23	0.90	60	2.3
UF15KC23 - __H	230	60	38	0.17	0.38	3400	8.3	293	23	0.90	60	2.3