

|                         |                            |
|-------------------------|----------------------------|
| <b>DATA SHEET</b>       | 52105270                   |
| <b>SKINDICHT® SHV-M</b> | valid from :<br>08.04.2009 |

The SKINDICHT® SHV-M is a water pressure-tight cable gland for extremely demanding applications.

The special conical seal element is pulled through the entire gland and thus ensures excellent compression strength and strain relief.



#### Component parts:

|                |                     |
|----------------|---------------------|
| Body:          | nickel plated brass |
| Dome nut:      | nickel plated brass |
| Cone seal:     | CR/NBR              |
| Pressure cone: | nickel plated brass |
| Flat washer:   | galvanized steel    |
| O-Ring:        | NBR                 |

#### Technical features:

|                    |                                                            |
|--------------------|------------------------------------------------------------|
| Connecting thread: | M 12x1,5 up to M 32x1,5 in acc. to DIN EN 60 423, table. 1 |
| Protection class:  | IP 68 – 10 bar test in acc. to EN 60 529                   |
| Temperature range: | - 20° C up to + 80° C                                      |

#### Other Characteristics:

gentle cable clamping  
Robust

#### Norm references:



For more information please see our current catalogue.

Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.

|                                      |                        |             |
|--------------------------------------|------------------------|-------------|
| elaborated by:<br>TE-VZ: M.Steinberg | Document: DB52105270EN | page 1 of 1 |
|--------------------------------------|------------------------|-------------|