


SYLVANIA**COMPACT
FLUORESCENT LAMP****GLOBE 20W****DIMENSIONS (mm)**

Cap Type: E27 - EN60061-1 sheet -7004-21

ELECTRICAL DATA¹

		<u>Nominal Value</u>	<u>Min.</u>	<u>Max.</u>
Lamp rated wattage	(W) :	20W		22.0W
Lamp operating voltage (rms)	(V) :	230-240V		
Lamp current	(mA) :	174 mA		
Power Factor	:		0.55	

OPERATING CONDITIONS:

Cap Rim temperature	(°C) :			80
Lamp Ambient Temperature	(°C) :		-10	50
Operating Position	:	Unrestricted		
Weight	(g) :	160g		

PERFORMANCE SPECIFICATIONS :

Starting time at 25°C	(s) :		1.5
Warm up Time to 60% stabilized light output	(s) :		120
² Switching Cycles (to 50% Failure)	:	10000	

LAMP LIFE³

Average life (IEC Test Cycle)	(h) :	10000
-------------------------------	-------	-------

<u>PHOTOMETRIC DATA:</u>	colour no.	Luminous Flux nominal value (lm)	CRI (Class)	Colour Temp. (K)	Energy Efficiency Class	ILCOS Code
Homelight Deluxe	827	1152	1b	2700	A	FBT-20/27/1b-E27-95/140

Attention: Lamps comply with EN 60 968 (Safety Requirements) and EN 60 969 (Performance Requirements) and CE Regulations.¹Measured according to EN 60 969, at 50 Hz, lamp aged 100h.²Switching Cycle ON time 30s; OFF time 150s, at rated Voltage.³Life test according to EN 60 969.

Issued by : R & D Noida
Date : 20.06.2011
Revision Date :

DATA SHEET

Specification No. : LD0001
Supersedes :
Page : 1 of 1

HAVELLS SYLVANIA reserves the right to change data and specification without notice.
Data for guidance only.

SYLVANIA