










FCIconnect.com

Copyright FCI




mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family QUICKIE
ltr	ecn	no	dr	date	tolerances unless otherwise specified	scale 8:1	title QUICKIE SHROUD
A	V41735	MDF	12/28/94	12/28/94	angles .XX±.01/.3		
B	V50149	MRC	2/8/95	2/8/95	linear .XXX±.005/.13		
C	M06-0282	AGS	7/22/06	7/22/06	0°±2° .xxxx±.0020/.051		
					dr M. FETROW 12/28/94		
					enr M. SMYK 12/28/94		
					chr M. SMYK 12/28/94		
					appd M. SMYK 12/28/94		
sheet index	revision sheet	C	C				dwg no 66247 sheet 1 of 2 size A3
		1	2				type Product Customer Drawing

	POS	DIM L	DIM M	DIM N	DIM P	STYLE
66247-001	2 X 5	.690/17.53	.600/15.24	.540/13.72	.130/3.30	A
-002	2 X 7	.890/22.61	.800/20.32	.740/18.80	.130/3.30	
-003	2 X 8	.990/25.15	.900/22.86	.840/21.34	.220/5.59	
-004	2 X 10	1.190/30.23	1.100/27.94	1.040/26.42	.220/5.59	
-005	2 X 13	1.490/37.85	1.400/35.56	1.340/34.04	.130/3.30	
-006	2 X 17	1.890/48.01	1.800/45.72	1.740/44.20	.130/3.30	
-007	2 X 20	2.190/55.63	2.100/53.34	2.040/51.82	.220/5.59	
-008	2 X 25	2.690/68.33	2.600/66.04	2.540/64.52	.130/3.30	
-009	2 X 30	3.190/81.03	3.100/78.74	3.040/77.22	.220/5.59	
-010	2 X 12	1.390/35.31	1.300/33.02	1.240/31.50	.220/5.59	
-011	2 X 15	1.690/42.93	1.600/40.64	1.540/39.12	.130/3.30	
-012	2 X 22	2.390/60.71	2.300/58.42	2.240/56.90	.220/5.59	
-013	2 X 18	UNAVAILABLE				
-014	2 X 28	UNAVAILABLE				A
-015	2 X 25	2.690/68.33	2.600/66.04	2.540/64.52	.130/3.30	B
66247-016	2 X 32	UNAVAILABLE				A



STYLE A
SCALE 4:1



STYLE B
SCALE 4:1

NOTES:

1. MATERIAL: 30% GLASS FILLED POLYESTER, FLAME RETARDANT PER UL 94V-0, COLOR: BLUE.
2. THE FIRST TWO CAVITY POSITIONS AND THE LAST TWO POSITIONS ARE IDENTIFIED BY NUMBER.
3. TRIANGULAR POSITION ONE INDICATOR LOCATED APPROXIMATELY AS SHOWN.
4. CENTER LINES OF .0300/.762 DIAMETER HOLES.
5. CENTER LINES OF .0360/.914 DIAMETER HOLES.
6. ROUND HOLE SIZES ALTERNATE BETWEEN .0300/.762 & .0360/.914 DIAMETER, SEE NOTES 4 & 5.

mat'l. code				surface ISO 1302	tolerance ISO 406 ISO 1101	projection INCH/MM	product family QUICKIE
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title
C					linear .XX±.01/.3 linear .xxx±.005/.13 0'±2' .xxxx±.0020/.051	INCH/MM	QUICKIE SHROUD
					dr M. FETROW 12/28/94	scale 8:1	
					enr M. SMYK 12/28/94		dwg no
					chr M. SMYK 12/28/94		66247 M.SMYK
					appd M. SMYK 12/28/94		sheet 2 of 2 size A3
sheet index	revision sheet						type Product Customer Drawing