



SIGUARD CABLE-OPERATED SWITCH METAL
HOUSING, 2X M20X1.5 1NO+1NC,
WITHOUT LATCHING WITH LED LAMP 24VDC,
RED

General technical details:

product designation		cable-operated switch
Supply voltage	V	24 ... 24
Number of indicator lights		1
Rope length / maximum	m	25
Product component / EMERGENCY STOP device		No
Item designation / according to DIN 40719 extendable after IEC 204-2 / according to IEC 750		S
Item designation / according to DIN EN 61346-2		S
Width	mm	52
Height	mm	164.5
Depth	mm	74.5

Enclosure:

Type of mounting		screw fixing
material / of the housing		metal
Color / of the top part of housing		grey

Contact:

Number of NC contacts / for auxiliary contacts	1
Number of NO contacts / for auxiliary contacts	1

Switching function / arresting lock	No
-------------------------------------	----

Certificates/approvals:

General Product Approval



ROTEST

Shipping Approval	other
-------------------	-------



ABS



BUREAU VERITAS

Lloyd's Register

LRS



PRS



RINA

[Manufacturer](#)

Ambient conditions:

Protection class IP	IP65
---------------------	------

Ambient temperature		
---------------------	--	--

- during operating °C -25 ... +70

Further information:

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrial-controls/mall>

CAx-Online-Generator

<http://www.siemens.com/cax>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3SE7150-2DD04/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3SE7150-2DD04

last change: Feb 6, 2012