



RCA PHONO JACKS: KLPX Series

RCA Phono Jack PCB Mount

Product Features

Audio Applications for Computers and Multimedia
Two Contact Cost Efficient Design
Right Angle and Vertical Mount Available

Performance Specifications

Materials and Finish

Housing

PBT Thermoplastic, UL94V-0 Rated

Terminals

Brass, Tin Plated

Electrical Characteristics

Contact Resistance

30 milliohms Max.

Insulation Resistance

100 Megohms Min.at 500V DC

Dielectric Withstanding Voltage

500V AC RMS for 1 Minute

Mechanical Characteristics

Insertion Force

0.3kg - 3.0kg

Extraction Force

0.3kg - 3.0kg

Durability

5000 Mating Cycles Min.

Operating Temperature

-25°C to +80°C

2D Drawing	IGES	STEP	3D PDF
Solder Profile	CofC RoHS Compliant	CofC REACH Compliant	UL Plastic File
Certificate of Origin	Check Stock	Request a Sample	Send Us An Email

Generated Part Number

Part Number Builder

	-			
Series		Type	Color Option	Plating Option

Series

KLPX - RCA Phono Jack

Type

0848-2 - Vertical Mount

0848A-2 - Right Angle Mount

Color Option

B - Black

R - Red

W - White

Y - Yellow

Barrel Plating Option


Blank - Nickel Plating

Contact Kycon for other options

KLPX

Dimensions in mm

KLPX-0848A-2-x



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kycon:](#)

[KLPX-0848-2-B](#) [KLPX-0848-2-R](#) [KLPX-0848-2-W](#) [KLPX-0848-2-Y](#) [KLPX-0848-2-B-G](#) [KLPX-0848-2-R-G](#) [KLPX-0848-2-Y-G](#) [KLPX-0848-2-W-G](#) [KLPX-0848A-2-R](#) [KLPX-0848A-2-B](#) [KLPX-0848A-2-Y](#) [KLPX-0848A-2-O](#) [KLPX-0848A-2-W](#) [KLPX-0848A-2-Y-G](#) [KLPX-0848A-2-W-G](#) [KLPX-0848A-2-B-G](#) [KLPX-0848A-2-R-G](#) [KLPX-0848A-2-BL](#) [KLPX-0848A-2-GR](#) [KLPX-0848A-2-O-G](#) [KLPX-0848-2-GR](#) [KLPX-0848-2-BL](#) [KLPX-0848-2-O](#) [KLPX-028-W](#) [KLPX-028-B](#) [KLPX-028-R](#)