

EURO PLUG




- Various lighting angles to select 40°, 60° and 80°. Standard lighting angle is 80°.
- Power of each LED bulb is 1W. (777-956 is 2W)
- Equipped with a LED driver for directly connecting to voltage of AC power. (100V~260V) (50Hz/60Hz) with plug.
- LED driver can be externally mounted for increasing LED bulbs.

- Reinforced lense for high crack-resistance.
- Well prevention for explosion, dust, coolant and lubricants.
- Furnished with 1.8 meters of cord without plug. (For low voltage)
- Long service life up to 40,000 lighting hours.
- Aluminum body.
- Applicable for semiconductor manufacturing equipment and clean room.
- Suitable for temperature range -30° ~ +60°
- Free of infrared ray and ultraviolet ray radiation.

DIMENSIONS

unit:mm



Unit: mm					
STOCK NO.	A	B	C	LED BULB QUANTITY	LIGHT OUTPUT
777-7956	298	340	332	6	780 lm
777-7965	480	522	514	12	1560 lm
777-7968	835	877	869	20	2860

