

Item no.: 770-205
Product description: SOCKET WITHOUT RELIEF HOUSING 5 POLE PIN
SPACING 10 MM / 0.394 IN 100% PROTECTED AGAINST
MISMATING



Produkt kann von Bild abweichen / product may differ

Packing unit 50 pieces

Product group	20 (WINSTA)
pole count	5
Cross section [mm ²]	0.5 - 4 mm ²
Cross section [AWG]	20 - 12 AWG
Connection method	CONTACT CAGE CLAMP [®] CONNECTION
Measured voltage EN	400 V
Measured shock voltage	6 kV
Pollution degree	3
Current intensity EN	25 A
Weight	15.71 g
Color	black
No. of connection Points	10
No. of potentials	5
Height	12.9 mm
Height	0.508 in
Width	50 mm
Width	1.969 in
Depth	37.5 mm
Depth	1.476 in

Strip length from
Strip length to
Strip length

9 mm
9 mm
0.35 in



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm²]
770-205	ABS	06-HG154986/11-PDA	400	25	0,5-4,0
770-205	CBCertificateVDE	DE1-29543	250/400	25	0,5-4
770-205	CCA	NL6677	400	25	0,5-4,0
770-205	cURus	E45171	600	20	12
770-205	DNV	E-9217	400	25	4
770-205	GL	42875-02HH	400	25	4
770-205	KEMA	2128605.02	400	25	0,5-4,0
770-205	LR	02/20050(E3)	250	25	2,5
770-205	PRS	TE/1719/880590/08	400	25	0,5-4,0
770-205	PSE	JET0695-43009-1002	600	20	12
770-205	VDE	Ausweis.Nr.30726	250/400	16/25	0,5-4,0

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected