

## PatchRunner™ Vertical Cable Management System

- High density minimizes area required for network layout, freeing up valuable floor space
- Curved cable management fingers support cables as they transition to the vertical pathway eliminating the need for horizontal managers
- Individual fingers can be removed without the use of a tool for routing of large cable bundles
- Fingers align with rack spaces simplifying cable routing
- Slack management spools organize and manage patch cord slack allowing standardization of patch cords
- Optional hinged doors provide easy access to vertical pathway; purchased separately from manager
- Available in 7 foot and 8 foot versions



PRV8

PRVF8



PRD

| Part Number                                                       | Part Description                                                                                                        | No. of Rack Spaces <sup>^</sup> | Std. Pkg. Qty. | Std. Ctn. Qty. |
|-------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------|---------------------------------|----------------|----------------|
| <b>Vertical Manager – Manage Cable on Front and Rear of Rack*</b> |                                                                                                                         |                                 |                |                |
| <b>PRV6*</b>                                                      | Vertical cable manager, spools are not included. Dimensions: 84"H x 6"W x 16.4"D (2133.6mm x 152.4mm x 416.6mm)         | 45                              | 1              | —              |
| <b>PRV8*</b>                                                      | Vertical cable manager, includes four PRSP7 slack spools. Dimensions: 83.9"H x 8.0"W x 16.4"D (2131mm x 203mm x 417mm)  | 45                              | 1              | —              |
| <b>PRV10*</b>                                                     | Vertical cable manager, includes four PRSP7 slack spools. Dimensions: 83.9"H x 10.0"W x 16.4"D (2131mm x 254mm x 417mm) | 45                              | 1              | —              |
| <b>PRV12*</b>                                                     | Vertical cable manager, includes four PRSP7 slack spools. Dimensions: 83.9"H x 12.0"W x 16.4"D (2131mm x 305mm x 417mm) | 45                              | 1              | —              |
| <b>PRV15*</b>                                                     | Vertical cable manager, includes four PRSP7 slack spools. Dimensions: 83.9"H x 15.0"W x 16.4"D (2131mm x 381mm x 417mm) | 45                              | 1              | —              |

### Vertical Manager – Manage Cable on Front of Rack Only\*

|                |                                                                                                                        |    |   |   |
|----------------|------------------------------------------------------------------------------------------------------------------------|----|---|---|
| <b>PRVF6*</b>  | Vertical cable manager, spools are not included. Dimensions: 83.9"H x 6.0"W x 9.7"D (2131mm x 152mm x 246mm)           | 45 | 1 | — |
| <b>PRVF8*</b>  | Vertical cable manager, includes four PRSP7 slack spools. Dimensions: 83.9"H x 8.0"W x 9.7"D (2131mm x 203mm x 246mm)  | 45 | 1 | — |
| <b>PRVF10*</b> | Vertical cable manager, includes four PRSP7 slack spools. Dimensions: 83.9"H x 10.0"W x 9.7"D (2131mm x 254mm x 246mm) | 45 | 1 | — |
| <b>PRVF12*</b> | Vertical cable manager, includes four PRSP7 slack spools. Dimensions: 83.9"H x 12.0"W x 9.7"D (2131mm x 305mm x 246mm) | 45 | 1 | — |
| <b>PRVF15*</b> | Vertical cable manager, includes four PRSP7 slack spools. Dimensions: 83.9"H x 15.0"W x 9.7"D (2131mm x 381mm x 246mm) | 45 | 1 | — |

### PatchRunner™ Doors

|               |                                                                                     |    |   |   |
|---------------|-------------------------------------------------------------------------------------|----|---|---|
| <b>PRD6*</b>  | Dual hinged metal door. Dimensions: 82.8"H x 6.1"W x 1.6"D (2104mm x 206mm x 40mm)  | 45 | 1 | — |
| <b>PRD8*</b>  | Dual hinged metal door. Dimensions: 82.8"H x 8.1"W x 1.6"D (2104mm x 206mm x 40mm)  | 45 | 1 | — |
| <b>PRD10*</b> | Dual hinged metal door. Dimensions: 82.8"H x 10.1"W x 1.6"D (2104mm x 257mm x 40mm) | 45 | 1 | — |
| <b>PRD12*</b> | Dual hinged metal door. Dimensions: 82.8"H x 12.1"W x 1.6"D (2104mm x 308mm x 40mm) | 45 | 1 | — |

<sup>^</sup>One rack space = 1.75" (44.45mm).

All product color is black.

\*For part numbers that fit 8' rack, add "96" to end of part number. Overall height for managers is 95.5" (2426mm). Overall door height is 94.4" (2399mm).

### PatchRunner™ Vertical Cable Management System (continued)



PRSHD8



PED



PEDK



PRSP7



CRTW



PREP

| Part Number | Part Description                                                                           | No. of Rack Spaces^ | Std. Pkg. Qty. | Std. Ctn. Qty. |
|-------------|--------------------------------------------------------------------------------------------|---------------------|----------------|----------------|
| PRD15*      | Dual hinged metal door.<br>Dimensions: 82.8"H x 15.1"W x 1.6"D<br>(2104mm x 384mm x 40mm)  | 45                  | 1              | —              |
| PRSHD6      | Single hinged metal door.<br>Dimensions: 80.7"H x 6.0"W x .8"D<br>(2049mm x 152mm x 20mm)  | 45                  | 1              | —              |
| PRSHD8      | Single hinged metal door.<br>Dimensions: 80.7"H x 8.0"W x .8"D<br>(2049mm x 203mm x 20mm)  | 45                  | 1              | —              |
| PRSHD12     | Single hinged metal door.<br>Dimensions: 80.7"H x 12.0"W x .8"D<br>(2049mm x 305mm x 20mm) | 45                  | 1              | —              |

#### PatchRunner™ High Capacity Dual Hinged Doors

|       |                                                                                                                                       |    |   |   |
|-------|---------------------------------------------------------------------------------------------------------------------------------------|----|---|---|
| PED6  | Dual hinged metal door.<br>Dimensions: 82.8"H x 6.1"W x 1.7"D<br>(2103mm x 155mm x 43mm)<br>Requires the use of PEDK6 door bracket.   | 45 | 1 | — |
| PED8  | Dual hinged metal door.<br>Dimensions: 82.8"H x 8.1"W x 1.7"D<br>(2103mm x 206mm x 43mm)<br>Requires the use of PEDK8 door bracket.   | 45 | 1 | — |
| PED10 | Dual hinged metal door.<br>Dimensions: 82.8"H x 10.1"W x 1.7"D<br>(2103mm x 256mm x 43mm)<br>Requires the use of PEDK10 door bracket. | 45 | 1 | — |
| PED12 | Dual hinged metal door.<br>Dimensions: 82.8"H x 12.1"W x 1.7"D<br>(2103mm x 307mm x 43mm)<br>Requires the use of PEDK12 door bracket. | 45 | 1 | — |

#### PED Door Brackets

|        |                                                               |   |   |    |
|--------|---------------------------------------------------------------|---|---|----|
| PEDK6  | Bracket kit for 6" wide PatchRunner™ Dual Hinged Door PED6.   | — | 1 | 10 |
| PEDK8  | Bracket kit for 8" wide PatchRunner™ Dual Hinged Door PED8.   | — | 1 | 10 |
| PEDK10 | Bracket kit for 10" wide PatchRunner™ Dual Hinged Door PED10. | — | 1 | 10 |
| PEDK12 | Bracket kit for 12" wide PatchRunner™ Dual Hinged Door PED12. | — | 1 | 10 |

#### Accessories

|        |                                                                                                                                                                                    |   |    |     |
|--------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---|----|-----|
| PRSP7  | Molded plastic slack spool, front only.<br>Dimensions: 7.0"D x 1.3" dia.<br>(178mm x 32mm)                                                                                         | — | 1  | 10  |
| PRSP5  | Molded plastic slack spool, front or rear.<br>Dimensions: 5.25"D x 1.3" dia. (133mm x 32mm)                                                                                        | — | 1  | 10  |
| PREP   | End panel<br>Dimensions: 82.5"H x 14.5"W x .7"D<br>(2095mm x 367mm x 18mm)                                                                                                         | — | 1  | —   |
| PREP96 | End panel 8'<br>Dimensions: 94.1"H x 14.5"W x .7"D<br>(2390mm x 367mm x 18mm)                                                                                                      | — | 1  | —   |
| CRTW   | Rack top trough with waterfall creates pathway above rack, for use with R2P, PRV6, PRV8, PRV10, PRV12, and PRV15.<br>Dimensions: 3.3"H x 23.4"W x 14.0"D<br>(84mm x 594mm x 356mm) | — | 1  | —   |
| WR5E-X | Snap-on finger cable retainers.                                                                                                                                                    | — | 10 | 100 |

^One rack space = 1.75" (44.45mm).

All product color is black.

\*For part numbers that fit 8' rack, add "96" to end of part number. Overall height for managers is 95.5" (2426mm). Overall door height is 94.4" (2399mm).