







- Übertragungseigenschaften nach ISO/IEC 11801:2002: Class D.
- Schutzart: IP20
- Temperaturbereich: -40°C ... +70°C
- Transmission properties in accordance with ISO/IEC 11801:2002: Class D.
- Protection level: IP20
- Temperature range: -40°C ... +70°C

AWG 22/7 schleppfähig/trailing	09 45 771 1183	100 m
AWG 22/7 schleppfähig/trailing	09 45 771 1178	50 m
AWG 22/7 schleppfähig/trailing	09 45 771 1175	20 m
AWG 22/7 schleppfähig/trailing	09 45 771 1173	10 m
AWG 22/7 schleppfähig/trailing	09 45 771 1168	5 m
AWG 22/7 schleppfähig/trailing	09 45 771 1166	3 m
AWG 22/7 schleppfähig/trailing	09 45 771 1164	1,5 m
AWG 22/7 flexibel/stranded	09 45 771 1161	100 m
AWG 22/7 flexibel/stranded	09 45 771 1156	50 m
AWG 22/7 flexibel/stranded	09 45 771 1153	20 m
AWG 22/7 flexibel/stranded	09 45 771 1151	10 m
AWG 22/7 flexibel/stranded	09 45 771 1127	5 m
AWG 22/7 flexibel/stranded	09 45 771 1125	3 m
AWG 22/7 flexibel/stranded	09 45 771 1123	1,5 m
AWG 22/1 massiv/solid	09 45 771 0061	100 m
AWG 22/1 massiv/solid	09 45 771 0056	50 m
AWG 22/1 massiv/solid	09 45 771 0053	20 m
AWG 22/1 massiv/solid	09 45 771 0051	10 m
AWG 22/1 massiv/solid	09 45 771 0027	5 m
AWG 22/1 massiv/solid	09 45 771 0025	3 m
AWG 22/1 massiv/solid	09 45 771 0023	1,5 m
massiv / flexibel solid / stranded	Bestell-Nr. Part-No.	Maß a Dim. a

Elektrische Prüfungen:
-Durchgang Pin to Pin + Schirm
-Kurzschluß
-Prüfspannung 500V/DC
electrical testing:
-pass Pin to Pin + shield
-short-circuit
-testing voltage 500V/DC

 All Dimensions in mm Original Size DIN A 3			Techn. Character.				Nicht tolerierte Maß/Free size tolerances				
				Dat.	Name	Maßstab/Scale 2:1	RJ1 Fieldpatchkabel, umgossen, <i>RJ1 fieldpatchcable, overmolded,</i> 4xAWG 22, IP20, 2x RJ45 plug				
			Detail.	19.08.04	Wie						
			Insp.	19.08.04	Wae						
			Stand.								
			HARTING Electronics GmbH & Co. KG					TB 09 45 771 1123			Blatt/ page /
32197			D-32339 ESPELKAMP								
Mod.	Dat.	Name					Sub.				