



CRYSTEK
MICROWAVE
A DIVISION OF CRYSTEK CORPORATION

RG-174 RF COAX CABLE ASSEMBLIES



RG174/U-50 Ohm Coaxial Cables

Features:

- Strain Relief:** Adhesive shrink tubing over crimp area
- Center Conductor:** 26 AWG bare copper covered steel
- Shielding:** Tinned copper braid (90% coverage)
- Insulation:** Polyethylene
- Jacket:** Black PVC
- Operating Temperature:** -40°C to +85°C

Part Number	Description	Lenth
CCSMA-MM-6	RG174 Cable, SMA Male/Male	6"
CCSMA-MM-12	RG174 Cable, SMA Male/Male	12"
CCSMA-MM-18	RG174 Cable, SMA Male/Male	18"
CCSMA-MM-24	RG174 Cable, SMA Male/Male	24"
CCSMA-MM-36	RG174 Cable, SMA Male/Male	36"
CCSMA-MM-48	RG174 Cable, SMA Male/Male	48"
CCBNS-MM-18	RG174 Cable, SMA/BNC Male/Male	18"
CCBNS-MM-36	RG174 Cable, SMA/BNC Male/Male	36"
CCADP-MM-6	RG174 Cable, SMA/2.1mm Male/Male	6"
CCSMACL-MC-24	RG174 Cable, SMA to Alligator Clips	24"
CCBNCCL-MC-30	RG174 Cable, BNC to Alligator Clips	30"



CRYSTEK
MICROWAVE
A DIVISION OF CRYSTEK CORPORATION

RG-174 RF COAX CABLE ASSEMBLIES



P/N: CCSMA-MM-xx



RG174/U Cable
SMA to SMA
Male/Male
Lenth(in): 6, 12, 18, 24,36,48
Features: Strain relief to both
SMA Connectors

P/N: CCBNS-MM-xx



RG174/U Cable
SMA to BNC
Male/Male
Lenth(in): 18, 36
Features: Strain relief to both
SMA and BNC Connector

P/N: CCADP-MM-6



RG174/U Cable
SMA to 2.1 mm Adapter Plug
Male/Male
Lenth(in): 6
Features: Strain relief to both
SMA and Plug Connector

P/N: CCBNCCL-MC-30



RG174/U Cable
BNC to Alligator Clips
Male/Clips
Lenth(in): 30
Features: Strain relief to both
Clip and SMA Connector

P/N: CCSMACL-MC-24



RG174/U Cable
SMA to Alligator Clips
Male/Clips
Lenth(in): 24
Features: Strain relief to both
Clip and SMA Connector