

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301080196](#)
Status: **Active**
Overview: [Wide-Area Lighting Products](#)
Description: Super-Safeway Wet Location 100W Fluorescent Tube Light with 4 Lamps, Cord Type 16/3 SOOW, Cord Length 7.62m (25.0')

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR85374
UL E174254

General

Product Family Portable Lighting
Series [130108](#)
NEMA Configuration NEMA 5-15
NEMA Rating NEMA 4X
Outlet Feed-Through
Overview [Wide-Area Lighting Products](#)
Product Name Super-Safeway
Type Wide Area Lamps
UPC 78678801713

Physical

Cord Length - Primary 7.62m (25.0')
Cord Length - Secondary 0.152m (6.00")
Depth 101.60mm (4.000")
Duty Industrial
Guard Included No
Guard Type N/A
Height N/A
Length 1.43m (56.250")
Material - Guard Nitrile Rubber 80 Shore A
Mounting Style Adjustable Brackets
Packaging Type Carton
Socket Construction N/A

Electrical

Bulb Type Fluorescent
Cord Type - Primary 16/3 SOOW
Lamp Type F25/T8
Lamp Wattage - Maximum 100W
Lumens 8320
On/Off Switch No
Voltage (Fixture) - Maximum 120VAC 60 HZ

Material Info

Engineering Number 2011



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130108](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION