





K44X Series Right Angle PCB Mount .590" Footprint

Pictured with Board Lock Option, Dimensions in mm [In]



Shell Size In mm	A ±.010 ±.025	A1 ±.010 ±.025	B ±.005 ±.013	C ±.015 ±.038
9 (E)	.643 16.33	.666 16.92	.984 24.99	1.213 30.81
15 (A)	.971 24.66	.994 25.25	1.312 33.32	1.541 39.14
25 (B)	1.511 38.38	1.534 38.96	1.852 47.04	2.088 53.04
37 (C)	2.159 54.84	2.182 55.42	2.500 63.50	2.729 69.32

A = Exterior of Female Shell (S) A1 = Interior of Male Shell (P)

D-SUBMINIATURE CONNECTORS

K44X Series

Documentation & Ordering Information

Kycon Part

Part Builder

Series	Shell Size	Contact Type	PCB Mounting Options	Front Panel Mounting Options	Plating Option
--------	------------	--------------	----------------------	------------------------------	----------------

Series

K44X - D-Subminiature Connector, Right Angle, PCB Termination, .590 Footprint

Shell Size-Contact Option


E - 9 Contacts
A - 15 Contacts
B - 25 Contacts
C - 37 Contacts

Contact Type


P - Pin Contact (Plug)
S - Socket Contact (Receptacle)

PC Board Mounting Option


P Option




Q Option




T Option



S Option




L Option




Front Panel Mounting Option


Standard J Option




R Option



T Option



JM Option



Plating Option

Blank - Gold Flash

30 - 30µ" Gold

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kycon:](#)

[K44X-A15P-Q](#) [K44X-B25P-P](#) [K44X-C37S-M15](#) [K44X-B25P-PJ](#) [K44X-E9S-Q](#) [K44X-E9S-Q30](#) [K44X-A15P-P](#) [K44X-A15S-P](#) [K44X-A15S-S](#) [K44X-A15S-SJ](#) [K44X-B25S-S](#) [K44X-E9P-S](#) [K44X-E9P-SR](#) [K44X-E9S-ST](#) [K44X-E9S-S](#)