

Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 112214

LTR.	REV.	RECORD	DATE
A			
B			
C			

MATERIAL :

INSULATOR : PBT + THERMOPLASTIC, 30% Glass
FILLED, UL 94V-0 RATED

CONTACT MATERIAL : PHOSPHOR BRONZE

ELECTRICAL CHARACTERISTICS:




CONTACT CURRENT RATING: 1AMPS

DIELECTRIC WITHSTANDING VOLTAGE: 750V AC MIN

CONTACT RESISTANCE : 30 MILLIOHMS MAX.

INSULATION RESISTANCE : 1000 MEGAOHMS MIN.

TEMPERATURE RATING : -55°C--+105°C



A176064	64	61.28	78.74	25.93	22.86
A176048	48	50.96	58.42	17.6	15.24
A176042	42	53.34	50.8		
A176040	40	50.8	48.26		
A176032	32	40.64	38.1		
A176028	28	35.56	33.02		
A176024	24	30.48	27.94	12.7	10.16
A174024	24	30.48	27.94		
A174022	22	27.94	25.4		
A173032	32	40.64	38.1		
A173028	28	35.56	33.02		
A173024	24	30.48	27.94	9.96	7.62
A173022	22	27.94	25.4		
A173020	20	25.4	22.86		
A173018	18	22.86	20.32		
A173016	16	20.32	17.78		
A173014	14	17.78	15.24	7.62	5.08
A173008	8	10.16	7.62		
A173006	6	7.62	5.08		
PART NO	PINS	A	B	C	D
	NO. OF	DIMENSIONS (UNIT:MM±0.2)			

Top Willing Co., Ltd.

DESCRIPTION			IC SOCKET SERIES		
3V6NO.			A170000		
TOLERANCE UNLESS OTHERWISE SPECIFIED					
LINEAR			±0.3 ±0.2 ±0.01		
ANGLES			±3°		
AUTHORITY	SIGNATURE	DATE			
DWN.	JAY	DESIGNED			
CHK.	ALEX	REVIEWED			
APVD.	JACKY	DESIGNED			
DWG KIND:	CUSTOMER	REV.	A 0	SCALE	1d
					SHEET 1 OF 1